



Wind Industrial Supplied

ADD: Unit One, Shuimu Lanting Building 1, No.105 Xiyang Rd., Xi'an, China
E-mail: sales@windindustrial.com paulyjiaren@hotmail.com
Http://www.windindustrial.com

Tel: +0086-029-8526 7416
Fax: +0086-029-8550 8192

NO.: _____

Wind industrial supplied company has been offering the oil and gas industries primarily in our capacity as a supplier. We manufacture many oil & gas drilling tools, oil & gas drilling equipment, oil drilling tools and completion tools for the petroleum and national gas fields abroad. We manufacture many varieties of standard and custom oil tools and down hole tooling and components. In addition to manufacturing and machining oil tools for our various clients.

Some of the products and services we offer are listed below.

Air Swivels, Augers, Casing, Casing System, Casing Puller, Coring tools, Core pipe, Cross Over Sub, Deck Bushing, Drill Collar, Drill pipe, Drill bits, Tri Cone Bits, PDC Bits, Claw Bits, Drag Bits, Claw Bits, Discharge Heads, Drive Shoes, Hammer Bits, Down Hole Hammer, Fishing Tools, Hole Openers, Kelly Cock, Lifting Sub and other Drilling supplies.

Metric Threaded rock drilling tools(Pitch 12mm)

产品名称 Name of product	钎头直径 Diam (mm)	合金 Tip size(mm)		边齿 倾角 Gauge button angle	水孔数 No.of flushing holes		重量 Weight (Kg)	型号 LHS P/N
		边齿 Gauge	正面 齿 Front		侧 Side	正 Front		
 柱齿形钎头 Button bits	48	3×11	2×9	35	1	1	0.7	ZQ48B-R3212B1
	55	3×14	1×12	35	1	1	0.9	ZQ55B-R3212B1
	60	3×14	2×12	40	1	1	0.9	ZQ60B4-R3212B1
	65	3×14	3×12	40	1	1	1.0	ZQ65B2-R3212B1
	70	3×14	3×12	35	1	1	1.6	ZQ70B-R3212B1
 柱齿形钎头 Button bits	55	4×10	2×10 1×10	35	1	1	0.8	ZQ55S1-R3212B1
	60	4×12	2×10 1×10	40	2	1	0.9	ZQ60S-R3212B1
		4×12	2×10 1×10	35	1	1	0.9	ZQ60S1-R3212B1
	65	4×12	2×12 1×12	40	1	1	1.1	ZQ65S-R3212B1
		4×14	2×12 1×10	40	1	1	1.2	ZQ65S1-R3212B1



Wind Industrial Supplied

ADD: Unit One, Shuimu Lanting Building 1, No.105 Xiyang Rd., Xi'an, China
E-mail: sales@windindustrial.com paulyjiaren@hotmail.com
Http://www.windindustrial.com

Tel: +0086-029-8526 7416
Fax: +0086-029-8550 8192

NO.: _____

 柱齿形钎头 Button bits	60	6×11	3×10	40	1	1	1.0	ZQ60D3-R3212
	65	6×12	3×12	35	1	1	1.2	ZQ65D-R3212
	70	6×12	3×12	35	1	1	1.4	ZQ70D-R3212
	75	6×12	5×10	35	2	1	1.7	ZQ75D-R3212
 十字形钎头 Cross bits	钎头直径 Diam (mm)	合金 Tip size(mm)					重量 Weight (Kg)	型号 LHS P/N
		高度×厚度 H×W						
	55	16×10					0.8	SQ55-R3212
	60	16×10					0.9	SQ60-R3212
	65	16×10					1.1	SQ65-R3212
	70	16×10					1.1	SQ70-R3212
	 丁形钎头 T-type bits	55	18×10					0.9
60		18×10					1.0	DQ60A-R3212
65		18×10					1.1	DQ65A-R3212
70		18×10					1.2	DQ70A-R3212
 风动钎杆 Round rods	长度 Length (mm)	直径 Diam (mm)		螺纹 Thread		重量 Weight (Kg)	型号 LHS P/N	
	600	Rd32		R3212-R3212		3.5	YG3212-06	
	800	Rd32		R3212-R3212		4.7	YG3212-08	
	1000	Rd32		R3212-R3212		5.8	YG3212-10	
	1100	Rd32		R3212-R3212		6.4	YG3212-11	
	1200	Rd32		R3212-R3212		7.0	YG3212-12	
 连接套 Coupling sleeves	150	45		R3212		1.1	LR3212-150	
	160	45		R3212		1.2	LR3212-160	



Wind Industrial Supplied

ADD: Unit One, Shuimu Lanting Building 1, No.105 Xiyang Rd., Xi'an, China

E-mail: sales@windindustrial.com paulyjiaren@hotmail.com

Http://www.windindustrial.com

Tel: +0086-029-8526 7416

Fax: +0086-029-8550 8192

NO.: _____

 钎尾 Shank adaptors	330		R3212	2.3	90-43A
	330		R3212	2.3	80-7

Rock tools for furnace

产品名称 Name of products	钎头 直径 Diam (mm)	合金 Tip size(mm) 高×厚 H×W	螺纹 Thread	重量 Weight (Kg)	型号 LHS P/N
 十字型钎头 Cross bits	45	7×8	R32	0.5	SQ45K-R32
	50	7×8	R32	0.6	SQ50K-R32
	55	7×8	R32	0.6	SQ55K-R32
	55	7×8	R38	0.7	SQ55K-R38
	55	7×8	T38	1.0	SQ55K-T38
	60	7×8	R32	0.7	SQ60K-R32
	60	7×8	R38	1.2	SQ60K-R38
	60	7×8	T38	1.3	SQ60K-T38
	65	7×8	R32	0.9	SQ65K-R32
	65	7×8	R38	1.3	SQ65K-R38
	65	7×8	T38	1.4	SQ65K-T38
	70	7×8	R32	1.3	SQ70K-R32
	70	7×8	T38	1.3	SQ70K-T38
	80	7×8	R32	1.7	SQ80K-R32
	100	7×8	R32	1.8	SQ100K-R32



Wind Industrial Supplied

ADD: Unit One, Shuimu Lanting Building 1, No.105 Xiyang Rd., Xi'an, China
E-mail: sales@windindustrial.com paulyjiaren@hotmail.com
Http://www.windindustrial.com

Tel: +0086-029-8526 7416
Fax: +0086-029-8550 8192

NO.: _____

产品名称 Name of product	钎头直径 Diam	边齿 Gauge	螺纹 Thread	重量 Weight	型号 LHS P/N
 柱齿形钎头 Button bits	48	4×10	R32	0.6	ZQ48S2-R32B1
	51	4×10	R32	0.7	ZQ51S2-R32B1
	54	4×11	R32	0.7	ZQ54S2-R32B1
	57	4×11	R32	0.8	ZQ57S2-R32B1
 耐用高炉杆 Durable furnace tapping rods	钎杆长度 Length	直径 Dia	螺纹 Thread	重量 Weight	型号 LHS P/N
	1700	38	R38-R30	15.5	YG38/30A-17K
	2000	38	R38-R30	16.4	YG38/30A-20K
	2500	38	R38-R30	20.4	YG38/30A-25K

 易耗高炉杆 Furnace tapping rods	1300	38	R32-R30	9.9	YG32/30A-13K
	1600	38	R32-R30	12.4	YG32/30A-16K
	1800	38	R32-R30	14.5	YG32/30A-18K
 整体式高炉杆 Integral furnace tapping rods	2800	38	R38-R32	22.7	YG38/32A-28K
	3400	38	R38-R32	27.8	YG38/32A-34K
	3600	38	R38-R32	29.4	YG38/32A-36K
	4100	38	R38-R32	34.5	YG38/32A-41K
	4300	38	R38-R32	35.3	YG38/32A-43K
 整体式高炉杆 Integral furnace tapping rods	3000	38	T38-T38	24.9	YGT38-30K
	3200	38	T38-T38	26.5	YGT38-32K
	4000	38	T38-T38	33.4	YGT38-40K