



Luminaire Catalogue

STANDARD[®]



01

DOWNLIGHT

LED Retro
LED Traditionnal
LED LPDL™
LED Presto
LED Gimbal
LED Lumeina
LED Commercial
LED Veloce™
Traditional

02

LED CEILING

Traditional
Shade
Brushed Nickel
Double Ring
Edge-Lit
Tri-Level

03

LED ACCENT LIGHTING

Armonia™ Slim Line Bar
Wall Sconce

04

LED RECESSED TROFFER

Panel
Center Basket
Retrokit

05

LED LINEAR

Striplight
Shoplight
Vapor Tight
Tri-proof

06

LED HIGH BAY

Bell Shape
Eco

07

LED OUTDOOR

Wall Pack
Wall Pack Slim
Flood and Area Light
Yard Light
Bollard
Canopy
Security Light

08

STEP DOWN TRANSFORMER

Compatibility list

LED Downlights

Residential

		Product highlights	Beam angle (°)	Colour temp. (K)
	Retro	• Retrofit only • E26 adaptor • Indoor / outdoor applications	100	2 700 3 000 4 000
	Traditional	• 2 installation options • Surface mount	113	2 700 3 000 4 000
	LPDL™	• Less than 1" thick • LED driver / jbox included • Warm-dim (from 3 000 K to 2 200 K) • IC rated	120	2 700 3 000-2 200 3 000 4 000 5 000
	Presto	• Integrated LED driver / jbox • Regressed look • 4 metal trim finishes available • IC rated	108	2 700 3 000 4 000
	Gimbal	• Up to 24° tilt • Small 1 1/2" aperture • LED driver / jbox included • Interchangeable trims • Warm-dim (from 3 000 K to 2 200 K) • IC rated	40	3 000-2 200 3 000 4 000
	Lumeina	• Reproduces the look of an MR16 halogen lamp • Interchangeable trims and reflectors • IC rated (6 W) • LED driver / jbox included	22 36 60	3 000

Commercial

	Commercial	• Retrofit only • Replaces HID and CFL	52	3 500 4 000
	Veloce™	• High light output • Defined beam with the clear lens (45°) or diffused lighting with the frosted lens (70°) • Interchangeable baffles (black or white) and reflector (silver) • LED driver / jbox included	45 70	3 000 3 500 4 000

Watts (W)	Volts (VAC)	Size (in.)	Shape	Life L70 (hrs)	Finish	Lumen output (lm)
10 12	120	4 5 and 6	Round	50 000	White	4" : 650 5"-6" : 850
10 12.5	120	4 6	Round	40 000	White Black Grey	4" : Up to 720 6" : Up to 850
7 9 12	120	3 4 6	Round Square	50 000	White Black Brushed nickel	3" : Up to 500 4" : Up to 600 6" : Up to 820
7 9	120	4 6	Round	40 000	White Black Silver Bronze	4" : Up to 638 6" : Up to 835
7	120	3 4	Round Square	Up to 36 000	White Black Brushed nickel	Up to 620
6 9	120	3 1/16 up to 4 7/16	Round Square	50 000	White White / Chrome Black / Chrome Silver / Chrome	6 W : 750 9 W : 950
18 27 40 54	120-277	6 8 10	Round	54 000	Stainless	18 W : 1 600 27 W : 2 400 40 W : 3 600 54 W : 4 900
13 18 26 38	120-277	4 6 8	Round	50 000	White with black or white baffle, or silver reflector	V4 13 W : 830 to 1 000 V6 18 W : 1 470 to 1 660 V6 26 W : 2 000 to 2 550 V8 26 W : 2 010 to 2 230 V8 38 W : 2 890 to 3 220



LED Retro

These LED Retro downlights offer a simple and economical option in any traditional downlight retrofit application. Easily replace the original lamp and trim with this LED solution and save on energy consumption and maintenance costs. With an E26 socket adaptor, this luminaire will fit in most traditional 4", 5" and 6" housings, and will be installed in no time.

- Perfect for both indoor and outdoor applications
- High CRI of 90 for great light output
- Regressed look to reduce glare




4"




5" - 6"

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Finish	Traditional equivalent (W)	Case qty (master)
4" Round											
66090	RDL4/10W/27K/WH/BAF/STD	10	120	2 700	681	≥90	50 000	100	White aluminum	50	20
66091	RDL4/10W/30K/WH/BAF/STD	10	120	3 000	712	≥90	50 000	100	White aluminum	50	20
66092	RDL4/10W/40K/WH/BAF/STD	10	120	4 000	713	≥90	50 000	100	White aluminum	50	20
5" - 6" Round											
66093 ¹	RDL6/12W/27K/WH/BAF/STD	12	120	2 700	852	≥90	50 000	100	White aluminum	65	10
66094 ¹	RDL6/12W/30K/WH/BAF/STD	12	120	3 000	877	≥90	50 000	100	White aluminum	65	10
66095 ¹	RDL6/12W/40K/WH/BAF/STD	12	120	4 000	892	≥90	50 000	100	White aluminum	65	10



4"



5" - 6"



DIMMABLE



QUICK CONNECT



RETROFIT



WET



TEMPERATURE



WARRANTY

CLASSIFIED²
UL US

ENERGY STAR


Lumen values are derived from photometric testing. For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com.
¹ 6" Retro downlight can be adjusted and installed in 5" or 6" traditional housings.
² This product complies with UL1598C standard for LED luminaire Retrofit kits.



LED Traditional

These dimmable LED downlight kits combine exceptional light output with the traditional downlight look. They are versatile and allow the user to easily convert most traditional recessed fixtures by installing them into a housing or installing them directly into a junction box.

- All mounting hardware is included for retrofit or new construction
- IC rated when used in an approved IC rated recessed housing



Easy installation using quick
access keyhole design





Retrofit Installation



J-Box Installation



Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Finish	Traditional equivalent (W)	Case qty (master)
4" Round											
63641	LED/DL4/10W/27K/RETRO/WH/STD	10	120	2 700	682	82	40 000	113	White	50	16
63642	LED/DL4/10W/27K/RETRO/BLK/STD	10	120	2 700	682	82	40 000	113	Black	50	16
63643	LED/DL4/10W/27K/RETRO/GRY/STD	10	120	2 700	682	82	40 000	113	Grey	50	16
63644	LED/DL4/10W/30K/RETRO/WH/STD	10	120	3 000	684	82	40 000	113	White	50	16
63645	LED/DL4/10W/30K/RETRO/BLK/STD	10	120	3 000	684	82	40 000	113	Black	50	16
63646	LED/DL4/10W/30K/RETRO/GRY/STD	10	120	3 000	684	82	40 000	113	Grey	50	16
63647	LED/DL4/10W/40K/RETRO/WH/STD	10	120	4 000	723	82	40 000	113	White	50	16
63648	LED/DL4/10W/40K/RETRO/BLK/STD	10	120	4 000	723	82	40 000	113	Black	50	16
63649	LED/DL4/10W/40K/RETRO/GRY/STD	10	120	4 000	723	82	40 000	113	Grey	50	16
6" Round											
63650	LED/DL6/12.5W/27K/RETRO/WH/STD	12.5	120	2 700	800	84	40 000	113	White	65	16
63653	LED/DL6/12.5W/30K/RETRO/WH/STD	12.5	120	3 000	809	84	40 000	113	White	65	16
63654	LED/DL6/12.5W/30K/RETRO/BLK/STD	12.5	120	3 000	809	84	40 000	113	Black	65	16
63655	LED/DL6/12.5W/30K/RETRO/GRY/STD	12.5	120	3 000	809	84	40 000	113	Grey	65	16
63656	LED/DL6/12.5W/40K/RETRO/WH/STD	12.5	120	4 000	853	84	40 000	113	White	65	16




Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com



LED LPDL™

LPDL™ (Low Profile Downlight) gives you all the flexibility you need during installation, especially in confined areas or when facing constraints such as wood beams, ceiling joist or air ducts. The driver is mounted separately from the light source which allows the luminaire profile to be less than 1" thick!



S1

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Finish	Traditional equivalent (W)	Case qty (master)
4" Round											
63879	LPDL4/RND/9W/27K/WH/STD	9	120	2 700	520	≥80	50 000	120	White	50	24
63882	LPDL4/RND/9W/30K/WH/STD	9	120	3 000	550	≥80	50 000	120	White	50	24
63884	LPDL4/RND/9W/30K/BN/STD	9	120	3 000	550	≥80	50 000	120	Brushed nickel	50	24
63883	LPDL4/RND/9W/30K/BK/STD	9	120	3 000	550	≥80	50 000	120	Black	50	24
63885	LPDL4/RND/9W/40K/WH/STD	9	120	4 000	580	≥80	50 000	120	White	50	24
63887	LPDL4/RND/9W/40K/BN/STD	9	120	4 000	580	≥80	50 000	120	Brushed nickel	50	24
63886	LPDL4/RND/9W/40K/BK/STD	9	120	4 000	580	≥80	50 000	120	Black	50	24
6" Round											
63864	LPDL6/RND/12W/30K/WH/STD	12	120	3 000	780	≥80	50 000	120	White	60	24
63866	LPDL6/RND/12W/30K/BN/STD	12	120	3 000	780	≥80	50 000	120	Brushed nickel	60	24
63867	LPDL6/RND/12W/40K/WH/STD	12	120	4 000	800	≥80	50 000	120	White	60	24
63869	LPDL6/RND/12W/40K/BN/STD	12	120	4 000	800	≥80	50 000	120	Brushed nickel	60	24



AIRTIGHT



DAMP



DIMMABLE



RATED



QUICK CONNECT



WARRANTY



Intertek



ENERGY STAR

Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com

LED LPDL™

S1

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Finish	Traditional equivalent (W)	Case qty (master)
3" Round Warm-Dim											
65858	LPDL3/RND/7W/30-22K/WH/W-DIM/STD	7	120	3 000-2 200	400	≥80	50 000	110	White	50	24
65859	LPDL3/RND/7W/30-22K/BN/W-DIM/STD	7	120	3 000-2 200	400	≥80	50 000	110	Brushed nickel	50	24
3" Round											
65851	LPDL3/RND/7W/30K/WH/STD	7	120	3 000	480	≥80	50 000	110	White	50	24
65852	LPDL3/RND/7W/30K/BN/STD	7	120	3 000	480	≥80	50 000	110	Brushed nickel	50	24
65853	LPDL3/RND/7W/40K/WH/STD	7	120	4 000	500	≥80	50 000	110	White	50	24
65854	LPDL3/RND/7W/40K/BN/STD	7	120	4 000	500	≥80	50 000	110	Brushed nickel	50	24
3" Square											
65855	LPDL3/SQR/7W/30K/WH/STD	7	120	3 000	430	≥80	50 000	110	White	50	24
65856	LPDL3/SQR/7W/30K/BN/STD	7	120	3 000	430	≥80	50 000	110	Brushed nickel	50	24
65857	LPDL3/SQR/7W/40K/WH/STD	7	120	4 000	450	≥80	50 000	110	White	50	24
4" Round Warm-Dim											
65364	LPDL4/RND/9W/30-22K/WH/W-DIM/STD	9	120	3 000-2 200	500	≥80	50 000	120	White	50	24
65365	LPDL4/RND/9W/30-22K/BN/W-DIM/STD	9	120	3 000-2 200	500	≥80	50 000	120	Brushed nickel	50	24
4" Round Wet Location											
65724	LPDL4/RND/9W/30K/WH/WET/STD	9	120	3 000	550	≥80	50 000	120	White	50	24
66220	LPDL4/RND/9W/30K/BN/WET/STD	9	120	3 000	550	≥80	50 000	120	Brushed nickel	50	24
65725	LPDL4/RND/9W/40K/WH/WET/STD	9	120	4 000	580	≥80	50 000	120	White	50	24
66221	LPDL4/RND/9W/40K/BN/WET/STD	9	120	4 000	580	≥80	50 000	120	Brushed nickel	50	24
4" Round											
65936	LPDL4/S2/RND/9W/27K/WH/STD	9	120	2 700	520	≥80	50 000	120	White	50	24
65937	LPDL4/S2/RND/9W/30K/WH/STD	9	120	3 000	550	≥80	50 000	120	White	50	24
65938	LPDL4/S2/RND/9W/30K/BN/STD	9	120	3 000	550	≥80	50 000	120	Brushed nickel	50	24
65939	LPDL4/S2/RND/9W/30K/BLK/STD	9	120	3 000	550	≥80	50 000	120	Black	50	24
65940	LPDL4/S2/RND/9W/40K/WH/STD	9	120	4 000	580	≥80	50 000	120	White	50	24
65941	LPDL4/S2/RND/9W/40K/BN/STD	9	120	4 000	580	≥80	50 000	120	Brushed nickel	50	24
65942	LPDL4/S2/RND/9W/40K/BLK/STD	9	120	4 000	580	≥80	50 000	120	Black	50	24
65943	LPDL4/S2/RND/9W/50K/WH/STD	9	120	5 000	600	≥80	50 000	120	White	50	24
4" Square											
65860	LPDL4/SQR/S2/9W/30K/WH/STD	9	120	3 000	550	≥80	50 000	120	White	50	24
65861	LPDL4/SQR/S2/9W/30K/BN/STD	9	120	3 000	550	≥80	50 000	120	Brushed nickel	50	24
65862	LPDL4/SQR/S2/9W/40K/WH/STD	9	120	4 000	580	≥80	50 000	120	White	50	24
65863	LPDL4/SQR/S2/9W/40K/BN/STD	9	120	4 000	580	≥80	50 000	120	Brushed nickel	50	24
6" Round Wet Location											
65726	LPDL6/RND/12W/30K/WH/WET/STD	12	120	3 000	780	≥80	50 000	120	White	60	24
65727	LPDL6/RND/12W/40K/WH/WET/STD	12	120	4 000	800	≥80	50 000	120	White	60	24
6" Round											
65946	LPDL6/S2/RND/12W/30K/WH/STD	12	120	3 000	780	≥80	50 000	120	White	60	24
65949	LPDL6/S2/RND/12W/30K/BN/STD	12	120	3 000	780	≥80	50 000	120	Brushed nickel	60	24
65947	LPDL6/S2/RND/12W/40K/WH/STD	12	120	4 000	800	≥80	50 000	120	White	60	24
65950	LPDL6/S2/RND/12W/40K/BN/STD	12	120	4 000	800	≥80	50 000	120	Brushed nickel	60	24
65948	LPDL6/S2/RND/12W/50K/WH/STD	12	120	5 000	820	≥80	50 000	120	White	60	24
6" Square											
65864	LPDL6/SQR/S2/12W/30K/WH/STD	12	120	3 000	780	≥80	50 000	120	White	60	24



AIRTIGHT



DAMP



DIMMABLE



IC RATED



QUICK CONNECT



WARM DIM



WET



5 YEARS WARRANTY




ETL Intertek




ENERGY STAR

Dimensions



Accessories

Order Code	Description	Opening diameter (in.)	Type	Case qty (master)
66049	ACC/MPLATE/3.625IN/SQR/STD	3 5/8	Square mounting plate	96
66056	ACC/MPLATE/3.625IN/ADJ/STD	3 5/8	Adjustable mounting plate	96
66051	ACC/MPLATE/4.25IN/SQR/STD	4 1/4	Square mounting plate	100
66058	ACC/MPLATE/4.25IN/ADJ/STD	4 1/4	Adjustable mounting plate	50
62678	ACC/MPLATE/4.25IN/HANG.BARS/STD	4 1/4	Mounting plate with hanger bars	20
64263	ACC/MPLATE/6.25IN/SQR/STD	6 1/4	Square mounting plate	96
64921	ACC/MPLATE/6.25IN/ADJ/STD	6 1/4	Adjustable mounting plate	24
64264	LPDL/ACC/6FT/EXTCABLE/STD	-	6' extension cord	96






LED Presto

Presto LED downlight is an all-in-one product that will fit seamlessly into all residential lighting applications. The base model is complete with a white baffle finish, but this line also offers trims made of stamped metal that will enhance the look of the luminaire, creating a sophisticated look tailored to your decor.



Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Finish	Traditional equivalent (W)	Case qty (master)
4" Round											
64326	LED/PRESTO/DL4ID/7W/27K/STD	7	120	2 700	590	81	40 000	107	White baffle	50	6
64327	LED/PRESTO/DL4ID/7W/30K/STD	7	120	3 000	630	82	40 000	108	White baffle	50	6
64328	LED/PRESTO/DL4ID/7W/40K/STD	7	120	4 000	638	83	40 000	108	White baffle	50	6
6" Round											
64329	LED/PRESTO/DL6ID/9W/30K/STD	9	120	3 000	805	82	40 000	108	White baffle	65	6




Accessories - Trims

Order code	Description	Finish	Type	Case qty (master)
4" Round				
64339	LED/PRESTO/ACC.TRIMS/DL4ID/WHT/STD	White	Smooth	120
64340	LED/PRESTO/ACC.TRIMS/DL4ID/BLK/STD	Black	Smooth	120
64341	LED/PRESTO/ACC.TRIMS/DL4ID/SLV/STD	Silver	Smooth	120
64342	LED/PRESTO/ACC.TRIMS/DL4ID/BRZ/STD	Bronze	Smooth	120
6" Round				
64343	LED/PRESTO/ACC.TRIMS/DL6ID/WHT/STD	White	Smooth	120
64346	LED/PRESTO/ACC.TRIMS/DL6ID/BLK/STD	Black	Smooth	120
64347	LED/PRESTO/ACC.TRIMS/DL6ID/SLV/STD	Silver	Smooth	120



Accessories

Order Code	Description	Opening diameter (in.)	Type	Case qty (master)
66051	ACC/MPLATE/4.25IN/SQR/STD	4 1/4	Square mounting plate	100
66058	ACC/MPLATE/4.25IN/ADJ/STD	4 1/4	Adjustable mounting plate	50
62678	ACC/MPLATE/4.25IN/HANG.BARS/STD	4 1/4	Mounting plate with hanger bars	20
64263	ACC/MPLATE/6.25IN/SQR/STD	6 1/4	Square mounting plate	96
64921	ACC/MPLATE/6.25IN/ADJ/STD	6 1/4	Adjustable mounting plate	24



AIRTIGHT



DIMMABLE



RATED



QUICK CONNECT



WET



5 YEARS WARRANTY



cULus



ENERGY STAR

Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and ENERGY STAR
qualified products, please visit www.standardpro.com

LED Gimbal



LED Gimbal Downlights are easy to install and allow you to direct the light where needed! The interchangeable trims offered in a variety of shapes, sizes and finishes, give you many options to choose from. Whether in new construction or in retrofit applications, the module and trim combination will fit any application!

- Small aperture designed for a sleek and glare free result
- Light output comparable to a PAR20 halogen lamp
- 24° tilt and 360° module rotation to light any direction




LED Modules and Drivers


Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	CBCP (cd)	Finish	Traditional equivalent (W)	Case qty (master)
Warm-Dim Module												
65981	LED/DL/GIMBAL/MOD/7W/30-22K/WH/STD	7	120	3 000-2 200	470	≥90	30 000	40	800	White	50	18
65982	LED/DL/GIMBAL/MOD/7W/30-22K/BN/STD	7	120	3 000-2 200	470	≥90	30 000	40	800	Brushed nickel	50	18
Module												
65420	LED/DL/GIMBAL/MOD/7W/30K/WH/STD	7	120	3 000	600	≥80	36 000	40	1 100	White	50	18
65422	LED/DL/GIMBAL/MOD/7W/30K/BN/STD	7	120	3 000	600	≥80	36 000	40	1 100	Brushed nickel	50	18
65421	LED/DL/GIMBAL/MOD/7W/40K/WH/STD	7	120	4 000	620	≥80	36 000	40	1 200	White	50	18
65423	LED/DL/GIMBAL/MOD/7W/40K/BN/STD	7	120	4 000	620	≥80	36 000	40	1 200	Brushed nickel	50	18

Trims


Order code	Description	Finish	Type	Case qty (master)
3" Round				
65432	LED/DL/GIMBAL/3IN/TRIM/RND/FLAT/WH/STD	White	Flat	96
65433	LED/DL/GIMBAL/3IN/TRIM/RND/FLAT/BN/STD	Brushed nickel	Flat	96
66230	LED/DL/GIMBAL/3IN/TRIM/RND/FLAT/BK/STD	Black	Flat	96
65450	LED/DL/GIMBAL/3IN/TRIM/RND/CURVED/WH/STD	White	Curved	96
65451	LED/DL/GIMBAL/3IN/TRIM/RND/CURVED/BN/STD	Brushed nickel	Curved	96
3" Square				
65434	LED/DL/GIMBAL/3IN/TRIM/SQR/FLAT/WH/STD	White	Flat	96
65435	LED/DL/GIMBAL/3IN/TRIM/SQR/FLAT/BN/STD	Brushed nickel	Flat	96
66231	LED/DL/GIMBAL/3IN/TRIM/SQR/FLAT/BK/STD	Black	Flat	96
4" Round				
65436	LED/DL/GIMBAL/4IN/TRIM/RND/FLAT/WH/STD	White	Flat	96
65437	LED/DL/GIMBAL/4IN/TRIM/RND/FLAT/BN/STD	Brushed nickel	Flat	96
66232	LED/DL/GIMBAL/4IN/TRIM/SQR/FLAT/BK/STD	Black	Flat	96
4" Square				
65438	LED/DL/GIMBAL/4IN/TRIM/SQR/FLAT/WH/STD	White	Flat	96
65439	LED/DL/GIMBAL/4IN/TRIM/SQR/FLAT/BN/STD	Brushed nickel	Flat	96
66233	LED/DL/GIMBAL/4IN/TRIM/SQR/FLAT/BK/STD	Black	Flat	96



Dimensions




Module



Module and Driver




Ø 2 3/4" (70 mm)




Ø 1 7/8" (47.5 mm)

3" Trim




Ø 1 7/8" (47.5 mm)

3" Trim




Ø 2 3/4" - 4 1/4" (70-108 mm)



Ø 1 7/8" (47.5 mm)

4" Trim



Ø 1 7/8" (47.5 mm)

4" Trim

Accessories

Order Code	Description	Opening diameter (in.)	Type	Case qty (master)
66020	ACC/MPLATE/2.75IN/SQR/STD	2 3/4	Square mounting plate	96
66021	ACC/MPLATE/2.75IN/ADJ/STD	2 3/4	Adjustable mounting plate	24
64264	LPDL/ACC/6FT/EXTCABLE/STD	-	6' extension cord	96



AIRTIGHT



DAMP



DIMMABLE



IC



QUICK
CONNECT



WARM DIM



5
YEARS
WARRANTY



ETL
Intertek



ENERGY
STAR





LED Lumeina

Lumeina Series is the perfect combination of state of the art technology and aesthetic design.

The quality of light of this series is comparable to that of a halogen lamp offering crisp, directional light which perfectly highlights surroundings. It offers a CRI of 90 and glare-control reflector design.

This small LED module provides higher lumen performance than an LED lamp and is very easy to install. Without the need of a housing, it is installed directly in the ceiling using torsion springs and most models are IC rated. The LED module is fitted with an external dimmable driver.

Lumeina is also offering style, discretion and flexibility with a wide selection of interchangeable trims and accessories.





LED Modules

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	CBCP (cd)	Traditional equivalent MR16 (W)	Case qty (master)
IC (can be used in insulated ceiling)											
64706	LUMEINA/MOD/IC/6W/30K/22/STD	6	120	3 000	750	≥90	50 000	22	3 051	50	20
64707	LUMEINA/MOD/IC/6W/30K/36/STD	6	120	3 000	750	≥90	50 000	36	1 763	50	20
64708	LUMEINA/MOD/IC/6W/30K/60/STD	6	120	3 000	750	≥90	50 000	60	1 078	50	20
Non-IC (not for use in insulated ceiling)											
64709	LUMEINA/MOD/9W/30K/22/STD	9	120	3 000	950	≥90	50 000	22	3 524	50	20
64710	LUMEINA/MOD/9W/30K/36/STD	9	120	3 000	950	≥90	50 000	36	2 121	50	20
64711	LUMEINA/MOD/9W/30K/60/STD	9	120	3 000	950	≥90	50 000	60	1 305	50	20

LED Drivers

	System watts (W)	Max. load (W)	Input Volts (VAC)	Output volts (VDC)	Input current (mA)
Lumeina 6 W	9	9	120	30-38	200
Lumeina 9 W	12	12	120	30-38	260



LED Driver 6 W and 9 W

Accessories

Order code	Description	Opening diameter (in.)	Type	Case qty (master)
66020	ACC/MPLATE/2.75IN/SQR/STD	2 ¾	Square mounting plate	96
66021	ACC/MPLATE/2.75IN/ADJ/STD	2 ¾	Adjustable mounting plate	24
66046	ACC/MPLATE/3IN/SQR/STD	3	Square mounting plate	96
66047	ACC/MPLATE/3.25IN/SQR/STD	3 ¼	Square mounting plate	96
62675	ACC/MPLATE/3.25IN/ADJ/STD	3 ¼	Adjustable mounting plate	50
62673	ACC/MPLATE/3.25IN/HANG.BARS/STD	3 ¼	Mounting plate with hanger bars	20
66048	ACC/MPLATE/3.5IN/SQR/STD	3 ½	Square mounting plate	96
66050	ACC/MPLATE/3.75IN/SQR/STD	3 ¾	Square mounting plate	96
62771	ACC/MPLATE/3.75IN/HANG.BARS/STD	3 ¾	Mounting plate with hanger bars	20
62672	ACC/INSULATED BOX/3_4.5/STD	3 to 4 ½	Insulated box with hanger bars	4



Lumen values are derived from photometric testing.
For a complete list of compatible dimmers, please visit www.standardpro.com
Lumeina 9 W can be used in insulated ceilings only when combined with the insulated box (62672)

Trims

Order code	Description	Type	Colour	Diameter		Cutting diameter		Compatible mounting plate	Case qty (master)
				(in.)	(mm)	(in.)	(mm)		

IC (can be used in insulated ceiling)

	64731	LUMEINA/TRIM/GMB.REC/WH/STD	Gimbal	White	3 17/32	90	3	77	66046	50
	64733	LUMEINA/TRIM/GMB.BAF/WH/STD	Gimbal	White	4 1/8	105	3 1/2	89	66048	50
	64735	LUMEINA/TRIM/SQR_RND/GMB/WH/SM/STD	Gimbal	White	4 7/16	113	3 1/8	80	62673 66047 62675	50
	64741	LUMEINA/TRIM/GMB.CURVED/WH/STD	Gimbal	White	4 11/32	110	3 3/4	95	66050 62771	50
	64742	LUMEINA/TRIM/SQR_RND/GMB/WH/LRG/STD	Gimbal	White	4 7/16	113	3 3/4	95	66050 62771	50
	64732 ^{1 2}	LUMEINA/TRIM/SWR/WH/STD	Shower	White	3 17/32	90	3	77	66046	50
	64734	LUMEINA/TRIM/D.BAF/WH/STD	Deep baffle	White	3 15/16	100	3 1/2	89	66048	50
	64736	LUMEINA/TRIM/SQR_RND/REC/WH/STD	Recessed	White	3 5/32	80	2 3/4	70	66020 66021	50
	64737	LUMEINA/TRIM/CURVED/WH/STD	Curved	White	3 1/16	78	2 3/4	70	66020 66021	50

Non-IC Accessory (not for use in insulated ceiling)

	64743	LUMEINA/TRIMEXT/STD	Trim extension	White	1 31/32	50	-	-	-	50
---	-------	---------------------	----------------	-------	---------	----	---	---	---	----

Order code	Description	Type	Colour	Diameter		Cutting diameter		Compatible mounting plate	Case qty (master)
			Trim / Baffle	(in.)	(mm)	(in.)	(mm)		

Non-IC (not for use in insulated ceiling)

	64738	LUMEINA/TRIM/RFL_WH/STD	Reflector	White / Chrome	3 17/32	90	3	77	66046	50
	64739	LUMEINA/TRIM/RFL_SLV/STD	Reflector	Silver / Chrome	3 17/32	90	3	77	66046	50
	64740	LUMEINA/TRIM/RFL_BLK/STD	Reflector	Black / Chrome	3 17/32	90	3	77	66046	50





LED Commercial


The commercial LCR downlight series is your best solution for an easy conversion of existing downlights to energy efficient LED. By using the LCR series to enhance your space, it provides a crisp light output while retaining a minimalist architectural look. A quick and simple retrofit solution for replacing existing CFL, HID, or incandescent luminaires without removing the existing frame.




Order code	Description	Watts	Volts	Colour temp.	Lumen output	CRI	Life L70	Beam angle	Traditional equivalent (W)		Finish	Case qty
		(W)	(VAC)	(K)	(lm)		(hrs)	(°)	CFL	HID		
6"												
64972	LCR/DL6/18W/35K/2/DD1/STD	18	120-277	3 500	1 611	≥80	54 000	52	36	-	Silver	1
64973	LCR/DL6/18W/40K/2/DD1/STD	18	120-277	4 000	1 624	≥80	54 000	52	36	-	Silver	1
64974	LCR/DL6/27W/35K/2/DD1/STD	27	120-277	3 500	2 348	≥80	54 000	52	57	-	Silver	1
64975	LCR/DL6/27W/40K/2/DD1/STD	27	120-277	4 000	2 366	≥80	54 000	52	57	-	Silver	1
8"												
64976	LCR/DL8/18W/35K/2/DD1/STD	18	120-277	3 500	1 653	≥80	54 000	52	36	-	Silver	1
64977	LCR/DL8/18W/40K/2/DD1/STD	18	120-277	4 000	1 678	≥80	54 000	52	36	-	Silver	1
64978	LCR/DL8/27W/35K/2/DD1/STD	27	120-277	3 500	3 408	≥80	54 000	52	57	-	Silver	1
64979	LCR/DL8/27W/40K/2/DD1/STD	27	120-277	4 000	2 471	≥80	54 000	52	57	-	Silver	1
64980	LCR/DL8/40W/40K/2/DD1/STD	40	120-277	4 000	3 587	≥80	54 000	52	-	100	Silver	1
10"												
64981	LCR/DL10/54W/40K/2/DD1/STD	54	120-277	4 000	4 884	≥80	54 000	52	-	150	Silver	1

Housing Compatibility


Model	Minimum housing dimensions (in.)	Maximum housing dimensions (in.)
6"	6	6 11/16
8"	7 25/32	8 7/8
10"	10	10 23/32




6"



8"



10"



LED Driver

Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and ENERGY STAR
qualified products, please visit www.standardpro.com



DAMP



DIMMABLE



RATING



RETROFIT



WARRANTY



UL US



ENERGY STAR



LED Veloce™



The range of Veloce™ LED downlights is an ideal solution to replace fixtures in existing installations as well as for use in new construction. As it operates on a 1-10 V dimming system, this series is best suited for commercial applications.

This series is available in 4", 6", and 8" replacement options, and it does not require the use of a housing. The LED module is fitted with an external dimmable driver and is mounted into the ceiling using torsion springs.

- High light output
- Defined beam with the clear lens (45°) or diffused lighting with the frosted lens (70°)
- Anti-glare reflector design
- Variety of interchangeable reflectors and baffles

LED Veloce™ 4



Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	CBCP (cd)	Baffle colour	Traditional equivalent (W)		Case qty (master)
											CFL	HID	
Clear Lens													
64744	VELOCE4/MOD/13W/30K/45/SLV/STD	13	120-277	3 000	1 000	≥90	50 000	45	1 648	Silver	26	20	4
64750	VELOCE4/MOD/13W/30K/45/BLK/STD	13	120-277	3 000	1 000	≥90	50 000	45	1 648	Black	26	20	4
64756	VELOCE4/MOD/13W/30K/45/WH/STD	13	120-277	3 000	1 000	≥90	50 000	45	1 648	White	26	20	4
64745	VELOCE4/MOD/13W/35K/45/SLV/STD	13	120-277	3 500	1 000	≥90	50 000	45	1 781	Silver	26	20	4
64751	VELOCE4/MOD/13W/35K/45/BLK/STD	13	120-277	3 500	1 000	≥90	50 000	45	1 781	Black	26	20	4
64757	VELOCE4/MOD/13W/35K/45/WH/STD	13	120-277	3 500	1 000	≥90	50 000	45	1 781	White	26	20	4
64746	VELOCE4/MOD/13W/40K/45/SLV/STD	13	120-277	4 000	1 000	≥90	50 000	45	1 756	Silver	26	20	4
64752	VELOCE4/MOD/13W/40K/45/BLK/STD	13	120-277	4 000	1 000	≥90	50 000	45	1 756	Black	26	20	4
64758	VELOCE4/MOD/13W/40K/45/WH/STD	13	120-277	4 000	1 000	≥90	50 000	45	1 756	White	26	20	4

Frosted Lens

64747	VELOCE4/MOD/F/13W/30K/70/SLV/STD	13	120-277	3 000	830	≥90	50 000	70	599	Silver	26	20	4
64753	VELOCE4/MOD/F/13W/30K/70/BLK/STD	13	120-277	3 000	830	≥90	50 000	70	599	Black	26	20	4
64759	VELOCE4/MOD/F/13W/30K/70/WH/STD	13	120-277	3 000	830	≥90	50 000	70	599	White	26	20	4
64748	VELOCE4/MOD/F/13W/35K/70/SLV/STD	13	120-277	3 500	830	≥90	50 000	70	624	Silver	26	20	4
64754	VELOCE4/MOD/F/13W/35K/70/BLK/STD	13	120-277	3 500	830	≥90	50 000	70	624	Black	26	20	4
64760	VELOCE4/MOD/F/13W/35K/70/WH/STD	13	120-277	3 500	830	≥90	50 000	70	624	White	26	20	4
64749	VELOCE4/MOD/F/13W/40K/70/SLV/STD	13	120-277	4 000	830	≥90	50 000	70	643	Silver	26	20	4
64755	VELOCE4/MOD/F/13W/40K/70/BLK/STD	13	120-277	4 000	830	≥90	50 000	70	643	Black	26	20	4
64761	VELOCE4/MOD/F/13W/40K/70/WH/STD	13	120-277	4 000	830	≥90	50 000	70	643	White	26	20	4

LED driver


	System watts (W)	Max. load (W)	Input volts (VAC)	Output volts (VDC)	Input current (mA)
Veloce 4	16	18	120-277	30-42	350



Ø 3 17/32" (90 mm) up to
Ø 4 1/4" (100 mm)

Accessories

Order code	Description	Opening diameter (in.)	Type	Case qty (master)
66051	ACC/MPLATE/4.25IN/SQR/STD	4 1/4	Mounting plate	100
66058	ACC/MPLATE/4.25IN/ADJ/STD	4 1/4	Adjustable mounting plate	50
62678	ACC/MPLATE/4.25IN/HANG.BARS/STD	4 1/4	Mounting plate with hanger bars	20
62672	ACC/INSULATED BOX/3_4.5/STD	3 to 4 1/2	Insulated box with hanger bars	4



DIMMABLE



DRY



LOW UNIFIED
GLARE RATING



5 YEARS
WARRANTY



Intertek

Lumen values are derived from photometric testing.
For a complete list of compatible dimmers, please visit www.standardpro.com

LED Veloce™ 6



Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	CBCP (cd)	Baffle colour	Traditional equivalent (W)		Case qty (master)
											CFL	HID	

Clear Lens

64762	VELOCE6/MOD/18W/35K/45/SLV/STD	18	120-277	3 500	1 660	≥90	50 000	45	2 328	Silver	2 x 26	30	4
64766	VELOCE6/MOD/18W/35K/45/BLK/STD	18	120-277	3 500	1 660	≥90	50 000	45	2 328	Black	2 x 26	30	4
64770	VELOCE6/MOD/18W/35K/45/WH/STD	18	120-277	3 500	1 660	≥90	50 000	45	2 328	White	2 x 26	30	4
64763	VELOCE6/MOD/18W/40K/45/SLV/STD	18	120-277	4 000	1 660	≥90	50 000	45	2 364	Silver	2 x 26	30	4
64767	VELOCE6/MOD/18W/40K/45/BLK/STD	18	120-277	4 000	1 660	≥90	50 000	45	2 364	Black	2 x 26	30	4
64771	VELOCE6/MOD/18W/40K/45/WH/STD	18	120-277	4 000	1 660	≥90	50 000	45	2 364	White	2 x 26	30	4
64774	VELOCE6/MOD/26W/35K/45/SLV/STD	26	120-277	3 500	2 250	≥90	50 000	45	3 121	Silver	2 x 32	50	4
64778	VELOCE6/MOD/26W/35K/45/BLK/STD	26	120-277	3 500	2 250	≥90	50 000	45	3 121	Black	2 x 32	50	4
64782	VELOCE6/MOD/26W/35K/45/WH/STD	26	120-277	3 500	2 250	≥90	50 000	45	3 121	White	2 x 32	50	4
64775	VELOCE6/MOD/26W/40K/45/SLV/STD	26	120-277	4 000	2 250	≥90	50 000	45	3 237	Silver	2 x 32	50	4
64779	VELOCE6/MOD/26W/40K/45/BLK/STD	26	120-277	4 000	2 250	≥90	50 000	45	3 237	Black	2 x 32	50	4
64783	VELOCE6/MOD/26W/40K/45/WH/STD	26	120-277	4 000	2 250	≥90	50 000	45	3 237	White	2 x 32	50	4

Frosted Lens

64764	VELOCE6/MOD/F/18W/35K/70/SLV/STD	18	120-277	3 500	1 470	≥90	50 000	70	980	Silver	2 x 26	30	4
64768	VELOCE6/MOD/F/18W/35K/70/BLK/STD	18	120-277	3 500	1 470	≥90	50 000	70	980	Black	2 x 26	30	4
64772	VELOCE6/MOD/F/18W/35K/70/WH/STD	18	120-277	3 500	1 470	≥90	50 000	70	980	White	2 x 26	30	4
64765	VELOCE6/MOD/F/18W/40K/70/SLV/STD	18	120-277	4 000	1 470	≥90	50 000	70	959	Silver	2 x 26	30	4
64769	VELOCE6/MOD/F/18W/40K/70/BLK/STD	18	120-277	4 000	1 470	≥90	50 000	70	959	Black	2 x 26	30	4
64773	VELOCE6/MOD/F/18W/40K/70/WH/STD	18	120-277	4 000	1 470	≥90	50 000	70	959	White	2 x 26	30	4
64776	VELOCE6/MOD/F/26W/35K/70/SLV/STD	26	120-277	3 500	2 000	≥90	50 000	70	1 331	Silver	2 x 32	50	4
64780	VELOCE6/MOD/F/26W/35K/70/BLK/STD	26	120-277	3 500	2 000	≥90	50 000	70	1 331	Black	2 x 32	50	4
64784	VELOCE6/MOD/F/26W/35K/70/WH/STD	26	120-277	3 500	2 000	≥90	50 000	70	1 331	White	2 x 32	50	4
64777	VELOCE6/MOD/F/26W/40K/70/SLV/STD	26	120-277	4 000	2 000	≥90	50 000	70	1 407	Silver	2 x 32	50	4
64781	VELOCE6/MOD/F/26W/40K/70/BLK/STD	26	120-277	4 000	2 000	≥90	50 000	70	1 407	Black	2 x 32	50	4
64785	VELOCE6/MOD/F/26W/40K/70/WH/STD	26	120-277	4 000	2 000	≥90	50 000	70	1 407	White	2 x 32	50	4

LED Drivers

	System watts (W)	Max. load (W)	Input volts (VAC)	Output volts (VAC)	Input current (mA)
Veloce 6 (18 W)	22	36	120-277	30-42	500
Veloce 6 (26 W)	30	36	120-277	30-42	700



Ø 6" (150 mm) up to
Ø 6 5/8" (165 mm)

Accessories

Order code	Description	Opening diameter (in.)	Type	Case qty (master)
64263	ACC/MPLATE/6.25IN/SQR/STD	6 1/4	Mounting plate	96
64921	ACC/MPLATE/6.25IN/ADJ/STD	6 1/4	Adjustable mounting plate	24



LED Veloce™ 8



Order code	Description	Watts	Volts	Colour temp.	Lumen output	CRI	Life L70	Beam angle	CBCP	Baffle colour	Traditional equivalent (W)		Case qty
		(W)	(VAC)	(K)	(lm)		(hrs)	(°)	(cd)		CFL	HID	(master)

Clear Lens

64786	VELOCE8/MOD/26W/35K/45/SLV/STD	26	120-277	3 500	2 230	≥90	50 000	45	2 517	Silver	2 x 32	50	4
64790	VELOCE8/MOD/26W/35K/45/BLK/STD	26	120-277	3 500	2 230	≥90	50 000	45	2 517	Black	2 x 32	50	4
64794	VELOCE8/MOD/26W/35K/45/WH/STD	26	120-277	3 500	2 230	≥90	50 000	45	2 517	White	2 x 32	50	4
64787	VELOCE8/MOD/26W/40K/45/SLV/STD	26	120-277	4 000	2 230	≥90	50 000	45	2 852	Silver	2 x 32	50	4
64791	VELOCE8/MOD/26W/40K/45/BLK/STD	26	120-277	4 000	2 230	≥90	50 000	45	2 852	Black	2 x 32	50	4
64795	VELOCE8/MOD/26W/40K/45/WH/STD	26	120-277	4 000	2 230	≥90	50 000	45	2 852	White	2 x 32	50	4
64798	VELOCE8/MOD/38W/40K/45/SLV/STD	38	120-277	4 000	3 220	≥90	50 000	45	4 092	Silver	2 x 42	70	4
64800	VELOCE8/MOD/38W/40K/45/BLK/STD	38	120-277	4 000	3 220	≥90	50 000	45	4 092	Black	2 x 42	70	4
64802	VELOCE8/MOD/38W/40K/45/WH/STD	38	120-277	4 000	3 220	≥90	50 000	45	4 092	White	2 x 42	70	4

Frosted Lens

64788	VELOCE8/MOD/F/26W/35K/70/SLV/STD	26	120-277	3 500	2 010	≥90	50 000	70	1 468	Silver	2 x 32	50	4
64792	VELOCE8/MOD/F/26W/35K/70/BLK/STD	26	120-277	3 500	2 010	≥90	50 000	70	1 468	Black	2 x 32	50	4
64796	VELOCE8/MOD/F/26W/35K/70/WH/STD	26	120-277	3 500	2 010	≥90	50 000	70	1 468	White	2 x 32	50	4
64789	VELOCE8/MOD/F/26W/40K/70/SLV/STD	26	120-277	4 000	2 010	≥90	50 000	70	1 601	Silver	2 x 32	50	4
64793	VELOCE8/MOD/F/26W/40K/70/BLK/STD	26	120-277	4 000	2 010	≥90	50 000	70	1 601	Black	2 x 32	50	4
64797	VELOCE8/MOD/F/26W/40K/70/WH/STD	26	120-277	4 000	2 010	≥90	50 000	70	1 601	White	2 x 32	50	4
64799	VELOCE8/MOD/F/38W/40K/70/SLV/STD	38	120-277	4 000	2 890	≥90	50 000	70	2 282	Silver	2 x 42	70	4
64801	VELOCE8/MOD/F/38W/40K/70/BLK/STD	38	120-277	4 000	2 890	≥90	50 000	70	2 282	Black	2 x 42	70	4
64803	VELOCE8/MOD/F/38W/40K/70/WH/STD	38	120-277	4 000	2 890	≥90	50 000	70	2 282	White	2 x 42	70	4


LED Drivers

	System watts (W)	Max. load (W)	Input volts (VAC)	Output volts (VDC)	Input current (mA)
Veloce 8 (26 W)	30	36	120-277	30-42	700
Veloce 8 (36 W)	42	50	120-277	22-38	1 050




Ø 8 1/16" (205 mm) up to
Ø 8 11/16" (220 mm)




Veloce™ 4



Veloce™ 6



Veloce™ 8



Veloce™ 4 and 6 Driver

Veloce™ 8 Driver



DIMMABLE



DRY



LOW UNIFIED
GLARE RATING



5 YEARS
WARRANTY



ETL
Intertek

Lumen values are derived from photometric testing.
For a complete list of compatible dimmers, please visit www.standardpro.com



Traditional

We have taken our years of lighting expertise and incorporated it into our line of high quality recessed fixtures designed with ease of installation and versatile lighting options in mind. Recessed fixtures provide convenient unobtrusive general lighting for residential and commercial applications, and with STANDARD's extensive assortment of trims and housings, you can create an unparalleled look. Our wide varieties of trims suit all applications and complement every decor. Paired with Canada's largest selection of LED lamps you will be sure to find the best combination for all your lighting needs.

3" Housing



Order code	Description	Opening diameter (in.)	Volts (VAC)	Socket	Case qty (master)
Remodeler - IC¹ / Non-IC					
63230	RF3in/REM0D/IC/GU10/STD	3	120	GU10	6

3" Trims

Compatible Lamps (MR16 GU10)



Order code	Description	Finish	Rotation angle (°)	Case qty (inner/master)
Recessed Die-Cast				
62700	RF3/TRIM/DIECAST.REC/CHR/STD	Chrome	N/A	6/24
62701	RF3/TRIM/DIECAST.REC/SAT.CHR/STD	Satin chrome	N/A	6/24
62699	RF3/TRIM/DIECAST.REC/WH/STD	White	N/A	6/24
Gimbal				
62711	RF3/TRIM/GMB/CHR/STD	Chrome	35	6/24
62715	RF3/TRIM/GMB/SAT.CHR/STD	Satin chrome	35	6/24
62703	RF3/TRIM/GMB/WH/STD	White	35	6/24
62719	RF3/TRIM/GMB/BLK/STD	Black	35	6/24
62707	RF3/TRIM/GMB/ORB/STD	Oil rubbed bronze	35	6/24
Gimbal				
62710	RF3/TRIM/SQR/GMB/CHR/STD	Chrome	35	6/24
62714	RF3/TRIM/SQR/GMB/SAT.CHR/STD	Satin chrome	35	6/24
62702	RF3/TRIM/SQR/GMB/WH/STD	White	35	6/24

Accessories

Order code	Description	Opening diameter (in.)	Type	Case qty (master)
66047	ACC/MPLATE/3.25IN/SQR/STD	3 1/4	Square mounting plates	96
62675	ACC/MPLATE/3.25IN/ADJ/STD	3 1/4	Adjustable mounting plates	50
62673	ACC/MPLATE/3.25IN/HANG.BARS/STD	3 1/4	Mounting plates with hanger bars	25



For complete warranty information, please visit www.standardpro.com
 Safety glass included, only to be installed with an open style lamp. Not suitable for LED technology.
¹ This housing is rated for both insulated ceilings (IC) and non-insulated ceilings (non-IC), however, only to be used with an LED lamp in an IC application.



DAMP



MAX. LAMP WATTAGE



MAX. LAMP WATTAGE



EXTENDED WARRANTY



WARRANTY



C US

4" Housings



Order code	Description	Opening diameter (in.)	Volts (VAC)	Socket	Case qty (master)
Remodeler					
62690	RF4in/REMOD/LOW.VOLT/GU5.3/STD	4	12	GU5.3	6
Remodeler - IC¹ / Non-IC					
63231	RF4in/REMOD/IC/GU10/STD	4	120	GU10	6
63232	RF4in/REMOD/IC/E26/STD	4	120	E26	6
New Construction					
62685	RF4in/NC/NON-IC/LOW.VOLT/GU5.3/STD	4	12	GU5.3	6
New Construction - IC¹ / Non-IC					
64335	RF4in/NC/IC_NON-IC/E26/STD	4	120	E26	4
64336	RF4in/NC/IC_NON-IC/GU10/STD	4	120	GU10	4
New Construction - IC Airtight					
62682	RF4in/NC/IC/LOW.VOLT/GU5.3/STD	4	12	GU5.3	4
62681	RF4in/NC/IC/GU10/STD	4	120	GU10	4
62680	RF4in/NC/IC/E26/STD	4	120	E26	4

4" Trims

Compatible Lamp (PAR20)

Order code	Description	Finish	Rotation angle (°)	Case qty (inner/master)
Gimbal				
62713	RF4/TRIM/GMB/CHR/PAR20/STD	Chrome	30	6/24
62717	RF4/TRIM/GMB/SAT.CHR/PAR20/STD	Satin chrome	30	6/24
62705	RF4/TRIM/GMB/WH/PAR20/STD	White	30	6/24
62721	RF4/TRIM/GMB/BLK/PAR20/STD	Black	30	6/24
62709	RF4/TRIM/GMB/ORB/PAR20/STD	Oil rubbed bronze	30	6/24
Slim Line				
62743	RF4/TRIM/SLML/CHR/PAR20/STD	Chrome	N/A	6/24
62744	RF4/TRIM/SLML/SAT.CHR/PAR20/STD	Satin chrome	N/A	6/24
62742	RF4/TRIM/SLML/WH/PAR20/STD	White	N/A	6/24
Recessed				
62752	RF4/TRIM/REC/SAT.CHR_ALU/PAR20/STD	Satin chrome / Aluminum	N/A	6/24
62753	RF4/TRIM/REC/SAT.CHR_BLK/PAR20/STD	Satin chrome / Black	N/A	6/24
62751	RF4/TRIM/REC/WH_BLK/PAR20/STD	White / Black	N/A	6/24
62750	RF4/TRIM/REC/WH_CHR/PAR20/STD	White / Chrome	N/A	6/24
62749	RF4/TRIM/REC/WH_WH/PAR20/STD	White / White	N/A	6/24
63393	RF4/TRIM/REC/BLK_BLK/PAR20/STD	Black / Black	N/A	6/24



DAMP

MAX. LAMP
WATTAGEMAX. LAMP
WATTAGEEXTENDED
WARRANTY

WARRANTY




C US

For complete warranty information, please visit www.standardpro.com
¹ This housing is rated for both insulated ceilings (IC) and non-insulated ceilings (non-IC), however, only to be used with an LED lamp in an IC application

4" Shower Trims


Compatible Lamp (PAR20)




Order code	Description	Finish	Rotation angle (°)	Case qty (inner/master)
Shower				
62739 ¹	RF4/TRIM/SWR/CHR/PAR20/STD	Chrome	N/A	6/24
62741 ¹	RF4/TRIM/SWR/SAT.CHR/PAR20/STD	Satin chrome	N/A	6/24
62737 ¹	RF4/TRIM/SWR/WH/PAR20/STD	White	N/A	6/24

4" Trims


Compatible Lamps (MR16 GU10, GU5.3, E26, PAR16)



Order code	Description	Finish	Rotation angle (°)	Case qty (inner/master)
Gimbal				
62716 ²	RF4/TRIM/SQR/GMB/SAT.CHR/MR16/STD	Satin chrome	35	6/24
62704 ²	RF4/TRIM/SQR/GMB/WH/MR16/STD	White	35	6/24



Gimbal				
62712 ²	RF4/TRIM/GMB/CHR/MR16/STD	Chrome	35	6/24
62718 ²	RF4/TRIM/GMB/SAT.CHR/MR16/STD	Satin chrome	35	6/24
62706 ²	RF4/TRIM/GMB/WH/MR16/STD	White	35	6/24
62720 ²	RF4/TRIM/GMB/BLK/MR16/STD	Black	35	6/24
62708 ²	RF4/TRIM/GMB/ORB/MR16/STD	Oil rubbed bronze	35	6/24



Recessed Gimbal				
62724 ²	RF4/TRIM/GMB.REC/SAT.CHR&AL/MR16/STD	Satin chrome / Satin aluminum	35	6/24
62725 ²	RF4/TRIM/GMB.REC/SAT.CHR_BLK/MR16/STD	Satin chrome / Black	35	6/24
62723 ²	RF4/TRIM/GMB.REC/WH_CHR/MR16/STD	White / Chrome	35	6/24
62722 ²	RF4/TRIM/GMB.REC/WH_WH/MR16/STD	White / White	35	6/24
63394 ²	RF4/TRIM/GMB.REC/BLK_BLK/MR16/STD	Black / Black	35	6/24



Wall Washer				
62755 ²	RF4/TRIM/SLIT/CHR/MR16/STD	Chrome	N/A	6/24
62756 ²	RF4/TRIM/SLIT/SAT.CHR/MR16/STD	Satin chrome	N/A	6/24
62754 ²	RF4/TRIM/SLIT/WH/MR16/STD	White	N/A	6/24



Retractable Elbow (MR16 GU53 lamps only)				
62758 ²	RF4/TRIM/RETRACT.ELB/CHR/MR16/STD	Chrome	80	6/24
62757 ²	RF4/TRIM/RETRACT.ELB/SAT.CHR/MR16/STD	Satin chrome	80	6/24
62759 ²	RF4/TRIM/RETRACT.ELB/WH/MR16/STD	White	80	6/24




For complete warranty information, please visit www.standardpro.com

¹ Not recommended for use in steam showers or when directly exposed to water.

² Safety glass included, only to be installed with an open lamp. Not suitable for LED technology

4" Shower Trims


Compatible Lamps (MR16 GU10, GU5.3, E26 and PAR16)



Order code	Description	Finish	Rotation angle (°)	Case qty (inner/master)
Shower				
62731 ¹	RF4/TRIM/SWR/SQR/CHR/MR16/STD	Chrome	N/A	6/24
62732 ¹	RF4/TRIM/SWR/SQR/SAT.CHR/MR16/STD	Satin chrome	N/A	6/24
62730 ¹	RF4/TRIM/SWR/SQR/WH/MR16/STD	White	N/A	6/24
Shower				
62734 ¹	RF4/TRIM/SWR/SQR_SQR/CHR/MR16/STD	Chrome	N/A	6/24
62735 ¹	RF4/TRIM/SWR/SQR_SQR/SAT.CHR/MR16/STD	Satin chrome	N/A	6/24
62733 ¹	RF4/TRIM/SWR/SQR_SQR/WH/MR16/STD	White	N/A	6/24
Shower				
62738 ¹	RF4/TRIM/SWR/CHR/MR16/STD	Chrome	N/A	6/24
62740 ¹	RF4/TRIM/SWR/SAT.CHR/MR16/STD	Satin chrome	N/A	6/24
62736 ¹	RF4/TRIM/SWR/WH/MR16/STD	White	N/A	6/24

Accessories

Order code	Description	Opening diameter (in.)	Type	Case qty (master)
62676	ACC/MPLATE/4.25IN/SQR/STD	4 1/4	Square mounting plate	50
62677	ACC/MPLATE/4.25IN/ADJ/STD	4 1/4	Adjustable mounting plate	100
62678	ACC/MPLATE/4.25IN/HANG.BARS/STD	4 1/4	Mounting plate with hanger bars	25
62679	ACC/VAPOR BARRIER/STD	-	Vapor barrier	25



DAMP

MAX. LAMP
WATTAGEEXTENDED
WARRANTY

WARRANTY



C US

For complete warranty information, please visit www.standardpro.com
¹ Not recommended for use in steam showers or when directly exposed to water

5" Housings



Order code	Description	Opening diameter (in.)	Volts (VAC)	Socket	Case qty (master)
Remodeler - IC Airtight					
64365	RF5in/REM0D/IC/E26/STD	5	120	E26	6
New Construction - IC Airtight					
64366	RF5in/NC/IC/E26/STD	5	120	E26	6

5" Trims

Compatible Lamps (PAR30SN, PAR30LN)



Order code	Description	Finish	Rotation angle (°)	Case qty (master)
Cone - Airtight				
64390	RF5/TRIM/CONE/BLK/PAR30/STD	Black	N/A	24
64391	RF5/TRIM/CONE/BR.NKL/PAR30/STD	Brushed nickel	N/A	24
64392	RF5/TRIM/CONE/WH/PAR30/STD	White	N/A	24
Gimbal				
64393	RF5/TRIM/GMB/BLK/PAR30/STD	Black	30	24
64394	RF5/TRIM/GMB/BR.NKL/PAR30/STD	Brushed nickel	30	24
64395	RF5/TRIM/GMB/WH/PAR30/STD	White	30	24
Reflector				
65525	RF5/TRIM/CONE/RFL_WH/PAR30/STD	White/Chrome	N/A	24
Shower				
65524 ¹	RF5/TRIM/SWR/WH/PAR30/STD	White	N/A	24

Accessory

Order code	Description	Opening diameter (in.)	Type	Case qty (master)
62679	ACC/VAPOR BARRIER/STD	-	Vapor barrier	25



For complete warranty information, please visit www.standardpro.com
¹ Not recommended for use in steam showers or when directly exposed to water


6" Housings



Order code	Description	Opening diameter (in.)	Volts (VAC)	Socket	Case qty (master)
Remodeler - IC Airtight					
64367 ¹	RF6in/REMOD/IC/E26/STD	6	120	E26	6
New Construction - IC Airtight					
64368 ²	RF6in/NC/IC/E26/STD	6	120	E26	6

6" Trims


Compatible Lamp (PAR38)



Order code	Description	Finish	Rotation angle (°)	Case qty (master)
Cone - Airtight				
64396	RF6/TRIM/CONE/BLK/PAR38/STD	Black	N/A	24
64397	RF6/TRIM/CONE/BR.NKL/PAR38/STD	Brushed nickel	N/A	24
64398	RF6/TRIM/CONE/WH/PAR38/STD	White	N/A	24
Gimbal				
64399	RF6/TRIM/GMB/BLK/PAR38/STD	Black	30	24
64400	RF6/TRIM/GMB/BR.NKL/PAR38/STD	Brushed nickel	30	24
64401	RF6/TRIM/GMB/WH/PAR38/STD	White	30	24

Accessories

Order code	Description	Opening diameter (in.)	Type	Case qty (master)
64921	ACC/MPLATE/6.25IN/ADJ/STD	6 1/4	Adjustable mounting plate	24
64263	ACC/MPLATE/6.25IN/SQR/STD	6 1/4	Square mounting plate	96
62679	ACC/VAPOR BARRIER/STD	-	Vapor barrier	25



DAMP



MAX. LAMP WATTAGE



MAX. LAMP WATTAGE



EXTENDED WARRANTY



WARRANTY



3 1/2" Outdoor Soffits

Compatible Lamps (PAR20¹, R20¹)



Order code	Description	Finish	Opening diameter (in.)	Volts (VAC)	Socket	Case qty (master)
Housings						
62691	RF3.5in/OUT.SOF/BLK/E26/STD	Black	3 1/2	120	E26	12
62692	RF3.5in/OUT.SOF/BRN/E26/STD	Brown	3 1/2	120	E26	12
62693	RF3.5in/OUT.SOF/CLAY/E26/STD	Clay	3 1/2	120	E26	12
62694	RF3.5in/OUT.SOF/WH/E26/STD	White	3 1/2	120	E26	12

Accessories

Order code	Description	Type	Finish	Opening diameter (in.)	Case qty (master)
62668	RF/ACC/BAF/3.5/BLK/OUT.SOF/STD	Baffle	Black	3 1/2	50
62669	RF/ACC/BAF/3.5/WH/OUT.SOF/STD	Baffle	White	3 1/2	50
62771	ACC/MPLATE/3.75IN/HANG.BARS/STD	Mounting plate with hanger bars	-	3 3/4	25
66050	ACC/MPLATE/3.75IN/SQR/STD	Square mounting plate	-	3 3/4	96



4 1/2" Outdoor Soffits

Compatible Lamps (BR30², PAR30³)



Order code	Description	Finish	Opening diameter (in.)	Volts (VAC)	Socket	Case qty (master)
Housings						
62695	RF4.5in/OUT.SOF/BLK/E26/STD	Black	4 1/2	120	E26	12
62696	RF4.5in/OUT.SOF/BRN/E26/STD	Brown	4 1/2	120	E26	12
62697	RF4.5in/OUT.SOF/CLAY/E26/STD	Clay	4 1/2	120	E26	12
62698	RF4.5in/OUT.SOF/WH/E26/STD	White	4 1/2	120	E26	12

Accessories

Order code	Description	Type	Finish	Opening diameter (in.)	Case qty (master)
62670	RF/ACC/BAF/4.5/BLK/OUT.SOF/STD	Baffle	Black	4 1/2	50
62671	RF/ACC/BAF/4.5/WH/OUT.SOF/STD	Baffle	White	4 1/2	50
62772	ACC/MPLATE/4.75IN/HANG.BARS/STD	Mounting plate with hanger bars	-	4 3/4	25
64338	ACC/MPLATE/4.75IN/SQR/STD	Square mounting plate	-	4 3/4	50



DAMP



MAX. LAMP WATTAGE



MAX. LAMP WATTAGE



MAX. LAMP WATTAGE



OUTDOOR



EXTENDED WARRANTY



WARRANTY



C US

Remodeler Kits

Lamp colour matches the trim colour



Order code	Description	Size (in.)	Finish	Case qty (master)
63166	K/RF3/GU10/GMB/WH/LED/STD	3	White	6
63483	K/RF3/GU10/GMB/SAT.CHR/LED/STD	3	Satin Chrome	6
63474	K/RF4/PAR20/GMB/WH/LED/STD	4	White	6
63475	K/RF4/PAR20/GMB/SAT.CHR/LED/STD	4	Satin Chrome	6
63476	K/RF4/GU10/GMB/WH/LED/STD	4	White	6
63477	K/RF4/GU10/GMB/SAT.CHR/LED/STD	4	Satin Chrome	6

Shower Kits

Designed to handle humid environments



Order code	Description	Size (in.)	Finish	Case qty (master)
64480	K/RF4/P16/SWR/CHR/LED/STD	4	Chrome	6
64481	K/RF4/P16/SWR/WH/LED/STD	4	White	6
64482	K/RF4/P16/SWR/SAT.CHR/LED/STD	4	Satin Chrome	6

New Construction Kit



Order code	Description	Size (in.)	Finish	Case qty (master)
64497	K/RF4/NC/PAR20/GMB/WH/LED/STD	4	White	1

Included in the box

Galvanized steel housing
Trim with a unique design for smooth and secure fitting
High quality LED lamp – stable light output and long life
Connectors, cable clamps
Cutting template



DAMP



DIMMABLE



WARRANTY



WARRANTY



For a complete list of ENERGY STAR qualified lamps, please visit www.standardpro.com
For complete warranty information, please visit www.standardpro.com



LED Ceiling Luminaire

Discover our LED ceiling luminaire line equipped with high quality integrated LEDs: they are an energy efficient solution with a life rating of over 50 000 hours. This line offers a pleasant, dimmable light making a great solution for any general lighting needs. Thanks to our variety of decorative options you can enjoy direct or indirect lighting fitting seamlessly into any commercial and residential installations.

LED Traditional

02



6", 8"



11", 14"




16", 18", 20", 22"


Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Size (in.)	Shape	Finish	Case qty (master)
6", 8"												
64154	LED/CL6/10W/30K/FM/RND/STD	10	120	3 000	600	80	50 000	120	6	Round	White	24
64155	LED/CL6/10W/40K/FM/RND/STD	10	120	4 000	600	80	50 000	120	6	Round	White	24
64156	LED/CL8/12W/30K/FM/RND/STD	12	120	3 000	800	80	50 000	120	8	Round	White	12
64157	LED/CL8/12W/40K/FM/RND/STD	12	120	4 000	800	80	50 000	120	8	Round	White	12
11", 14"												
65598	LED/CL11/15W/27K/FM/RND/STD	15	120	2 700	1 050	80	50 000	120	11	Round	White	4
63298	LED/CL11/15W/30K/FM/RND/STD	15	120	3 000	1 050	80	50 000	120	11	Round	White	4
63299	LED/CL11/15W/40K/FM/RND/STD	15	120	4 000	1 000	80	50 000	120	11	Round	White	4
63300	LED/CL11/15W/30K/FM/SQR/STD	15	120	3 000	1 050	80	50 000	120	11	Square	White	4
63301	LED/CL11/15W/40K/FM/SQR/STD	15	120	4 000	1 000	80	50 000	120	11	Square	White	4
65599	LED/CL14/25W/27K/FM/RND/STD	25	120	2 700	1 700	80	50 000	120	14	Round	White	4
63302	LED/CL14/25W/30K/FM/RND/STD	25	120	3 000	1 700	80	50 000	120	14	Round	White	4
63303	LED/CL14/25W/40K/FM/RND/STD	25	120	4 000	1 650	80	50 000	120	14	Round	White	4
63304	LED/CL14/25W/30K/FM/SQR/STD	25	120	3 000	1 700	80	50 000	120	14	Square	White	4
63305	LED/CL14/25W/40K/FM/SQR/STD	25	120	4 000	1 650	80	50 000	120	14	Square	White	4
16", 18", 20", 22"												
65665	LED/CL16/26W/30K/FM/RND/STD	26	120	3 000	2 034	80	50 000	120	16	Round	White	4
65666	LED/CL16/26W/40K/FM/RND/STD	26	120	4 000	2 170	80	50 000	120	16	Round	White	4
65667	LED/CL18/32W/30K/FM/RND/STD	32	120	3 000	2 644	80	50 000	120	18	Round	White	4
65668	LED/CL18/32W/40K/FM/RND/STD	32	120	4 000	2 898	80	50 000	120	18	Round	White	4
65661	LED/CL20/37W/30K/FM/RND/STD	37	120	3 000	3 098	80	50 000	120	20	Round	White	2
65662	LED/CL20/37W/40K/FM/RND/STD	37	120	4 000	3 144	80	50 000	120	20	Round	White	2
65663	LED/CL22/40W/30K/FM/RND/STD	40	120	3 000	3 424	80	50 000	120	22	Round	White	2
65664	LED/CL22/40W/40K/FM/RND/STD	40	120	4 000	3 534	80	50 000	120	22	Round	White	2

Replacement Lenses

Order code	Description	Replacement for
64867	LED/CL6/LENS/RND/STD	64154, 64155
64868	LED/CL8/LENS/RND/STD	64156, 64157
64869	LED/CL11/LENS/RND/STD	63298, 63299, 65598
64877	LED/CL11/LENS/SQR/STD	63300, 63301
64878	LED/CL14/LENS/RND/STD	63302, 63303, 65599
64879	LED/CL14/LENS/SQR/STD	63304, 63305



11": 3" (76.2 mm)
 14": 3" (76.2 mm)
 16": 4 3/8" (111 mm)
 18": 4 3/16" (106 mm)
 20": 4 11/32" (110 mm)
 22": 4 3/16" (106 mm)



DAMP



DIMMABLE



WARRANTY



Lumen values are derived from photometric testing
 For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com


Shade

Our shades create a warm and elegant atmosphere. They complement our 11" and 14" LED traditional ceiling luminaires and are offered in assorted materials and textures which allows you to create a specific ambient style.

- Drum profile only
- Materials and textures available: silk type, cork, wood, and linen type



Order code	Description	Shape	Material	Finish	Compatible luminaire	Case qty (master)
For 11" Luminaires						
65681	LED/CL11/SHADE/RND/WHITE/STD	Round	Linen type	White	65598, 63298, 63299	6
65682	LED/CL11/SHADE/RND/BEIGE/STD	Round	Linen type	Beige	65598, 63298, 63299	6
65683	LED/CL11/SHADE/RND/BLACK/STD	Round	Linen type	Black	65598, 63298, 63299	6
65684	LED/CL11/SHADE/RND/DGRAY/STD	Round	Linen type	Grey	65598, 63298, 63299	6
65685	LED/CL11/SHADE/RND/WOOD/STD	Round	Wood	Wood	65598, 63298, 63299	6
65686	LED/CL11/SHADE/RND/CORK/STD	Round	Cork	Cork	65598, 63298, 63299	6
65687	LED/CL11/SHADE/RND/WFROST/STD	Round	Silk type	White frosted	65598, 63298, 63299	6
66044	LED/CL11/SHADE/RND/BRNW/STD	Round	Wood	Barn wood	65598, 63298, 63299	6
For 14" Luminaires						
65688	LED/CL14/SHADE/RND/WHITE/STD	Round	Linen type	White	65599, 63302, 63303	6
65689	LED/CL14/SHADE/RND/BEIGE/STD	Round	Linen type	Beige	65599, 63302, 63303	6
65690	LED/CL14/SHADE/RND/BLACK/STD	Round	Linen type	Black	65599, 63302, 63303	6
65691	LED/CL14/SHADE/RND/DGRAY/STD	Round	Linen type	Grey	65599, 63302, 63303	6
65692	LED/CL14/SHADE/RND/WOOD/STD	Round	Wood	Wood	65599, 63302, 63303	6
65693	LED/CL14/SHADE/RND/CORK/STD	Round	Cork	Cork	65599, 63302, 63303	6
65694	LED/CL14/SHADE/RND/WFROST/STD	Round	Silk type	White Frosted	65599, 63302, 63303	6
66045	LED/CL14/SHADE/RND/BRNW/STD	Round	Wood	Barn wood	65599, 63302, 63303	6



2
YEARS
WARRANTY

LED Brushed Nickel



6", 8"





11", 14"

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Finish	Case qty (master)
6" Round										
64247	LED/CLBN5.75/10W/30K/FM/RND/STD	10	120	3 000	550	80	50 000	120	Brushed nickel	24
64248	LED/CLBN5.75/10W/40K/FM/RND/STD	10	120	4 000	550	80	50 000	120	Brushed nickel	24
8" Round										
64249	LED/CLBN7.75/12W/30K/FM/RND/STD	12	120	3 000	750	80	50 000	120	Brushed nickel	12
64250	LED/CLBN7.75/12W/40K/FM/RND/STD	12	120	4 000	750	80	50 000	120	Brushed nickel	12
11" Round										
64095	LED/CLBN11/15W/30K/FM/RND/STD	15	120	3 000	1 200	80	50 000	120	Brushed nickel	4
64096	LED/CLBN11/15W/40K/FM/RND/STD	15	120	4 000	1 200	80	50 000	120	Brushed nickel	4
14" Round										
64099	LED/CLBN14/25W/30K/FM/RND/STD	25	120	3 000	2 000	80	50 000	120	Brushed nickel	4
64100	LED/CLBN14/25W/40K/FM/RND/STD	25	120	4 000	2 000	80	50 000	120	Brushed nickel	4

Replacement Lenses

Order code	Description	Replacement for
64880	LED/CLBN5.75/LENS/RND/STD	64247, 64248
64881	LED/CLBN7.75/LENS/RND/STD	64249, 64250
64882	LED/CLBN11/LENS/RND/STD	64095, 64096
64883	LED/CLBN14/LENS/RND/STD	64099, 64100



DAMP



DIMMABLE



WARRANTY




Lumen values are derived from photometric testing
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com

LED Double Ring



12", 14", 16"

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Finish	Case qty (master)
12" Round										
65605	LED/CLDR/BN/12/20W/30K/FM/RND/STD	20	120	3 000	1 525	80	50 000	120	Brushed nickel	4
65606	LED/CLDR/BN/12/20W/40K/FM/RND/STD	20	120	4 000	1 531	80	50 000	120	Brushed nickel	4
14" Round										
65607	LED/CLDR/BN/14/25W/30K/FM/RND/STD	25	120	3 000	1 875	80	50 000	120	Brushed nickel	4
65608	LED/CLDR/BN/14/25W/40K/FM/RND/STD	25	120	4 000	1 931	80	50 000	120	Brushed nickel	4
16" Round										
65611	LED/CLDR/BN/16/26W/30K/FM/RND/STD	26	120	3 000	1 849	80	50 000	120	Brushed nickel	2
65612	LED/CLDR/BN/16/26W/40K/FM/RND/STD	26	120	4 000	2 007	80	50 000	120	Brushed nickel	2



Lumen values are derived from photometric testing
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com



LED Edge-Lit

The LED Edge-Lit ceiling luminaire has a very slim design for a modern and minimalist look. These thin luminaires are equipped with an LED edge-lit technology to eliminate hot spots on the surface and provide a crisp and even light. Offered in a variety of shapes and sizes, it will fit any application.

- Easy twist-lock installation
- No visible screws
- Safety cable included
- Frosted polycarbonate lens





6", 8", 12"



6", 8", 12"


Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Finish	Case qty (master)
6" Round									
65454	LED/CL6/EDGELIT/11W/30K/FM/RND/WH/STD	11	120	3 000	855	≥80	50 000	White	20
65455	LED/CL6/EDGELIT/11W/40K/FM/RND/WH/STD	11	120	4 000	896	≥80	50 000	White	20
6" Square									
65460	LED/CL6/EDGELIT/11W/30K/FM/SQR/WH/STD	11	120	3 000	852	≥80	50 000	White	20
65461	LED/CL6/EDGELIT/11W/40K/FM/SQR/WH/STD	11	120	4 000	893	≥80	50 000	White	20
8" Round									
65456	LED/CL8/EDGELIT/14W/30K/FM/RND/WH/STD	14	120	3 000	1 066	≥80	50 000	White	20
65457	LED/CL8/EDGELIT/14W/40K/FM/RND/WH/STD	14	120	4 000	1 118	≥80	50 000	White	20
8" Square									
65462	LED/CL8/EDGELIT/14W/30K/FM/SQR/WH/STD	14	120	3 000	1 065	≥80	50 000	White	20
65463	LED/CL8/EDGELIT/14W/40K/FM/SQR/WH/STD	14	120	4 000	1 115	≥80	50 000	White	20
12" Round									
65458	LED/CL12/EDGELIT/22W/30K/FM/RND/WH/STD	22	120	3 000	1 647	≥80	50 000	White	10
65459	LED/CL12/EDGELIT/22W/40K/FM/RND/WH/STD	22	120	4 000	1 725	≥80	50 000	White	10
12" Square									
65464	LED/CL12/EDGELIT/22W/30K/FM/SQR/WH/STD	22	120	3 000	1 636	≥80	50 000	White	10
65465	LED/CL12/EDGELIT/22W/40K/FM/SQR/WH/STD	22	120	4 000	1 713	≥80	50 000	White	10




LED Tri-Level

Dimming technology maximizes energy savings by intelligently managing illumination levels to avoid wasted energy. The luminaire is controlled by a motion sensor that triggers light levels from low to high upon occupancy, and users can adjust the luminaire's standby light levels by percentage of light, lux and dimming delay of full output.


Perfect for lighting applications that require illumination 24/7, this technology represents a significant energy savings opportunity.




1. When there is sufficient natural light and a presence is detected the luminaire will not turn on, it will stay dimmed.



2. With insufficient natural light, the light is switched on automatically when presence is detected; it will remain on at 100% during the motion hold-time.




3. If no presence is detected the light dims to 10% and 30% (options) stand-by levels after the hold time.



4. Optional: Light switches off automatically after the stand-by period has elapsed.

Order code	Description	Watts (W)	Volts (V)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Sensor type	Finish	Case qty (master)
65723	LED/CL11TLEV/12W/40K/FM/RND/STD	12	120	4 000	1 020	80	50 000	120	Dim or Off	White	4

11" Round



DAMP



DIMMABLE



WARRANTY



Intertek



ENERGY STAR

Lumen values are derived from photometric testing
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com



LED Design Lighting

Create a cozy atmosphere or emphasize a specific element of your decor with STANDARD's Design and Accent Lighting line. It is widely versatile and adapts perfectly to several types of decor, whether it's a classical, industrial, modern or eclectic style.



LED Armonia™ Slim Line Bar


These LED Armonia™ Slim Line Bars are the perfect fit for multiple applications whether residential or commercial, such as undercabinet lighting, cove lighting, shelves and work stations. These interconnectable LED bars are easy to install and assemble. These bars neatly define contours of shapes with or without interruption and they ensure high quality lighting. The Armonia™ series allows you to build a system that is adapted to your needs without any cutting or soldering.

- Aluminum housing and polycarbonate frosted lens produces a soft light
- Constant current design will ensure the brightness and colour consistency from end-to-end
- Linkable bars that provide a continuous lighting
- Slim design – Thickness of 9 mm
- Maximum run in length: 26.2 ft. (8 m)
- Maximum power run: 120 W
- Dimmable




LED Slim Line Bars

Order code	Description	Watts (W)	Volts (VDC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Case qty (inner/master)
5.9"									
64576	LUCS/5.9IN/2.5W/27K/STD	2.5	24	2 700	180	82	25 000	120	4/40
64577	LUCS/5.9IN/2.5W/30K/STD	2.5	24	3 000	200	82	25 000	120	4/40
64578	LUCS/5.9IN/2.5W/40K/STD	2.5	24	4 000	210	82	25 000	120	4/40
11.8"									
64579	LUCS/11.8IN/5W/27K/STD	5	24	2 700	400	82	25 000	120	4/40
64580	LUCS/11.8IN/5W/30K/STD	5	24	3 000	420	82	25 000	120	4/40
64581	LUCS/11.8IN/5W/40K/STD	5	24	4 000	450	82	25 000	120	4/40
23.6"									
64582	LUCS/23.6IN/9W/27K/STD	9	24	2 700	700	82	25 000	120	4/40
64583	LUCS/23.6IN/9W/30K/STD	9	24	3 000	750	82	25 000	120	4/40
64584	LUCS/23.6IN/9W/40K/STD	9	24	4 000	760	82	25 000	120	4/40
39.3"									
64585	LUCS/39.3IN/15W/27K/STD	15	24	2 700	1 100	82	25 000	120	4/40
64586	LUCS/39.3IN/15W/30K/STD	15	24	3 000	1 200	82	25 000	120	4/40
64587	LUCS/39.3IN/15W/40K/STD	15	24	4 000	1 250	82	25 000	120	4/40



Included in the box

- 5.9" – 1 middle connector and 1 fixing clip – 180°
 11.8" / 23.6" – 1 middle connector and 2 fixing clips – 180°
 39.3" – 1 middle connector and 3 fixing clips – 180°



Lumen values are derived from photometric testing.
 For a complete list of compatible dimmers, please visit www.standardpro.com
 For a flat installation, remove the knockouts on both ends of the LED bar

Power Supplies

These LED bars can be dimmed directly at the bar using the cable connector with dimmer switch and a plug-in non-dimmable power supply or directly with a wall dimmer using a harwire dimmable power supply.




Hardwire




Plug-in


Order code	Description	Watts (W)	Volts (VDC)	Output volts (VDC)	Input current (mA)	Output current (mA)	Frequency (Hz)	Finish	VDC connector (Yes/No)	Waterproof (Yes/No)	Case qty (master)
Hardwire - Dimmable											
64864 ¹	LUC/PS/50W/24VDC/HW/D/STD	50	100-240	24	1 600	2 100	50/60	White	Yes	No	10
64865 ^{1 2 3}	LUC/PS/80W/24VDC/HW/D/STD	80	100-240	24	1 450	3 330	50/60	Black	Yes	Yes	10
64866 ^{1 2}	LUC/PS/120W/24VDC/HW/D/STD	120	100-240	24	2 000	5 000	50/60	Black	Yes	Yes	10
Plug-in - Non-dimmable											
64573 ⁴	LUC/PS/36W/24VDC/PLUG/STD	36	100-240	24	1 200	1 500	50/60	Black	Yes	No	25
64574 ⁴	LUC/PS/60W/24VDC/PLUG/STD	60	100-240	24	1 200	2 500	50/60	Black	Yes	No	25
64575 ⁴	LUC/PS/120W/24VDC/PLUG/STD	120	100-240	24	1 600	5 000	50/60	Black	Yes	No	20




64864




64865




64866



64573



64574



64575




DRY

IP66
RATING

WET


2
YEARS
WARRANTY3
YEARS
WARRANTY

Accessories



Order code	Description	Type	Figure	Length		Case qty (master)
				(in.)	(mm)	
Cable connectors						
64557	LUCS/ACC/CBL/STD	Cable connector without switch	A	22 ³ / ₁₆	563.5	100
64558	LUCS/ACC/CBL/TOUCH/STD	Cable connector with touch switch	A	22 ³ / ₁₆	563.5	100
64559	LUCS/ACC/CBL/SENSOR/STD	Cable connector with sensor switch	A	22 ³ / ₁₆	563.5	100
64560	LUCS/ACC/CBL/DIM/STD	Cable connector with dimmable switch	A	22 ³ / ₁₆	563.5	100
Accessories						
64561	LUCS/ACC/MIDCNT/STD 2P	Middle connector	B	-	-	500
64562	LUCS/ACC/CBL/EXT/STD	36" extension cable	C	36	914	50
64564	LUCS/ACC/LCORNERCNT/STD	Left corner connector	D	-	-	200
64565	LUCS/ACC/LCORNERCNT/STD	Right corner connector	E	-	-	200
64566	LUCS/ACC/VERTICALCNT/STD	Vertical connector (90°)	F	-	-	200
64863	LUCS/ACC/4WAY/STD	Extension cable - four ways	G	20	520	50
Mounting options						
64554	LUCS/ACC/FIXCLIP180/STD 2P	180° fixing clips	H	-	-	500
64555	LUCS/ACC/FIXCLIPADJUST/STD 2P	Adjustable fixing clips	I	-	-	500
64556	LUCS/ACC/TAPE10CM/STD 2P	3M tape (10 cm)	J	-	-	500
Jumpers						
64563	LUCS/ACC/JUMPER 19"/STD	19" jumper	K	19	483	100
64967	LUCS/ACC/JUMPER 54"/STD	54" jumper	L	54	1 372	100

Order code	Description	Figure	Watts (W)	Volts (VDC)	Colour temp. (K)	CRI	Lumen output (lm)	Beam angle (°)	Case qty (master)
Light connectors 3.7"									
64567	LUCS/ACC/LIGHTEDCNT/27K/STD	M	1	24	2 700	82	80	120	100
64568	LUCS/ACC/LIGHTEDCNT/30K/STD	M	1	24	3 000	82	90	120	100
64569	LUCS/ACC/LIGHTEDCNT/40K/STD	M	1	24	4 000	82	100	120	100



Light connector



Lumen values are derived from photometric testing
For a complete list of compatible dimmers, please visit www.standardpro.com



LED Wall Sconce

STANDARD's LED wall sconces adapt to a variety of applications. These modern style luminaires operate on line voltage and provide a diffused direct lighting of high quality due to it's 90+ CRI value.


They also come equipped with double-sided frosted lenses; depending on the desired look, they can be installed with a glossy or mat lens finish.




Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Beam angle (°)	Finish	Case qty (master)
Single										
65838	SVAN/SINGLE/10W/30K/BN/F/STD	10	120	3 000	628	≥90	50 000	120	Brushed nickel	12
65839	SVAN/SINGLE/10W/40K/BN/F/STD	10	120	4 000	669	≥90	50 000	120	Brushed nickel	12
Double										
65840	SVAN/DOUBLE/20W/30K/BN/F/STD	20	120	3 000	1 266	≥90	50 000	120	Brushed nickel	12
65841	SVAN/DOUBLE/20W/40K/BN/F/STD	20	120	4 000	1 344	≥90	50 000	120	Brushed nickel	12
Triple										
65842	SVAN/TRIPLE/30W/30K/BN/F/STD	30	120	3 000	1 917	≥90	50 000	120	Brushed nickel	6
65843	SVAN/TRIPLE/30W/40K/BN/F/STD	30	120	4 000	2 023	≥90	50 000	120	Brushed nickel	6
Quadruple										
65844	SVAN/QUAD/40W/30K/BN/F/STD	40	120	3 000	2 579	≥90	50 000	120	Brushed nickel	6
65845	SVAN/QUAD/40W/40K/BN/F/STD	40	120	4 000	2 422	≥90	50 000	120	Brushed nickel	6

Replacement Lens


Order code	Description	Finish	Case qty (inner/master)
65959	SVAN/LENS/F/STD	Frosted	10/200




Single



Double



Triple



Quadruple



DIMMABLE



RATING



WARRANTY



Intertek



ENERGY STAR

Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com



LED Recessed Troffer

04

Transform your lighting into an exquisite balance of refined appearance and superior efficiency.

Our wide variety of quality recessed troffers is perfect for any commercial application. They are perfectly suited for offices, as the well distributed light enhances productivity and reduces fatigue.



LED Panel

Our universal edge-lit LED panels are equipped with an innovative LED driver that operates from 120 V to 347 V. Regardless of the needs of your application, each unit is universal and can be installed in multiple locations.



1' x 4'




2' x 2'



2' x 4'

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Case qty (master)
1' x 4'								
66087	LPAN/S2/1X4/120-347V-DIM/40W/35K/STD	40	120-347	3 500	5 000	80	≥121 000	2
66088	LPAN/S2/1X4/120-347V-DIM/40W/40K/STD	40	120-347	4 000	5 000	80	≥121 000	2
66089	LPAN/S2/1X4/120-347V-DIM/40W/50K/STD	40	120-347	5 000	5 000	80	≥121 000	2
2' x 2'								
65542	LPAN/S2/2X2/120-347V-DIM/40W/35K/STD	40	120-347	3 500	5 200	80	≥121 000	4
65543	LPAN/S2/2X2/120-347V-DIM/40W/40K/STD	40	120-347	4 000	5 200	80	≥121 000	4
65544	LPAN/S2/2X2/120-347V-DIM/40W/50K/STD	40	120-347	5 000	5 200	80	≥121 000	4
2' x 4'								
65545	LPAN/S2/2X4/120-347V-DIM/50W/35K/STD	50	120-347	3 500	6 500	80	≥121 000	2
65546	LPAN/S2/2X4/120-347V-DIM/50W/40K/STD	50	120-347	4 000	6 500	80	≥121 000	2
65547	LPAN/S2/2X4/120-347V-DIM/50W/50K/STD	50	120-347	5 000	6 500	80	≥121 000	2



Accessories

Order code	Description	Type
64825	LPAN/ACC/2X2/SMK/STD	Surface mount kit
64826	LPAN/ACC/1X4/SMK/STD	Surface mount kit
64827	LPAN/ACC/2X4/SMK/STD	Surface mount kit
64828	LPAN/ACC/2X2/SUSPENSION/STD	Suspension cable
64829	LPAN/ACC/1X4_2X4/SUSPENSION/STD	Suspension cable
63490	DRYWALL KIT FOR 1X4 FRT/STD	Drywall kit
63491	DRYWALL KIT FOR 2X4 FRT/STD	Drywall kit




Lumen values are derived from photometric testing
For a complete list of compatible dimmers and DLC qualified products, please visit www.standardpro.com
¹ Estimated life hours

LED Center Basket


The LRCB series of luminaires has a direct/indirect center-diffuser that provides an optimal modern alternative to traditional fluorescent recessed luminaires. Their modern sleek look provides a smooth and visually comfortable lighting that eliminates surface shadows.




Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Case qty (master)
1' x 4'								
65550	LRCB/S2/1X4/120-277V-DIM/35W/35K/STD	35	120-277	3 500	4 480	80	≥100 000	1
65551	LRCB/S2/1X4/120-277V-DIM/35W/40K/STD	35	120-277	4 000	4 515	80	≥100 000	1
65552	LRCB/S2/1X4/120-277V-DIM/35W/50K/STD	35	120-277	5 000	4 550	80	≥100 000	1
2' x 2'								
65553	LRCB/S2/2X2/120-277V-DIM/35W/35K/STD	35	120-277	3 500	4 375	80	≥100 000	1
65554	LRCB/S2/2X2/120-277V-DIM/35W/40K/STD	35	120-277	4 000	4 410	80	≥100 000	1
65555	LRCB/S2/2X2/120-277V-DIM/35W/50K/STD	35	120-277	5 000	4 445	80	≥100 000	1
2' x 4'								
65556	LRCB/2X4/S2/120-277V-DIM/46W/35K/STD	46	120-277	3 500	5 750	80	≥100 000	1
65557	LRCB/2X4/S2/120-277V-DIM/46W/40K/STD	46	120-277	4 000	5 796	80	≥100 000	1
65558	LRCB/2X4/S2/120-277V-DIM/46W/50K/STD	46	120-277	5 000	5 842	80	≥100 000	1



1' x 4'



2' x 2'



2' x 4'

Accessories

Order code	Description	Type
63490	DRYWALL KIT FOR 1X4 FRT/STD	Drywall kit
63491	DRYWALL KIT FOR 2X4 FRT/STD	Drywall kit



Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and DLC qualified products, please visit www.standardpro.com
¹Estimated life hours



DAMP



DIMMABLE



WARRANTY




LED Retrokit


Use the conversion kit to modernize your existing fluorescent luminaires to convert and upgrade to LED. Improve the look of your ceiling with its architectural design without the need to break in the ceiling. Achieve instant savings by reducing installation and maintenance costs.




Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Case qty (master)
2' x 2'								
65362	LRT/RETRO/2X2/120-277V-DIM/40W/40/STD	40	120-277	4 000	4 700	85	≥100 000	4
2' x 4'								
65363	LRT/RETRO/2X4/120-277V-DIM/50W/40/STD	50	120-277	4 000	6 050	85	≥100 000	4



2' x 2'



2' x 4'



Driver

Lumen values are derived from photometric testing
For a complete list of compatible dimmers and DLC qualified products, please visit www.standardpro.com
¹Estimated life hours



DIMMABLE



RETROFIT



WARRANTY





LED Linear


Our linear line is the best choice to replace traditional fluorescent strip luminaires with our integrated LED solution. Modernize your application with these efficient alternatives to traditional technology.




LED Striplight

These high quality luminaires are equipped with a frosted lens that diffuses the light comfortably. This series is a great option for retrofitting your traditional fluorescent linear luminaires to balance performance, aesthetics, and cost.


Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Case qty (master)
2'								
65034	LSS/2FT/20W/40K/120-277/STD	20	120-277	4 000	2 600	80	≥100 000	6
4'								
65035	LSS/4FT/41W/40K/120-277/STD	41	120-277	4 000	5 330	80	≥100 000	6



2'



4'



2', 4'

Accessories

Order code	Description	Type
66084	LSS/ACC/2FT/LENS/STD	Replacement lens for 2ft
66085	LSS/ACC/4FT/LENS/STD	Replacement lens for 4ft
66086	LSS/ACC/VHOOKCHAIN/STD	Hanger kit

Lumen values are derived from photometric testing
For a complete list of compatible dimmers and DLC qualified products, please visit www.standardpro.com
¹Estimated life hours



Tri-Level Programmable Striplight



This tri-level programmable striplight has been designed to prevent energy loss in applications or spaces that require continuous lighting.

The luminaire increases energy savings while allowing users to wisely manage levels of luminosity in a given space. It features an integrated micro-wave motion sensor that regulates light levels according to occupancy of the space



05

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	Lumens per watts (W)	CRI	Life L70 (hrs)	Case qty (master)
66083	LSS/4FT/TLEV/32W/40K/120-277/A1/STD	32	120-277	4 000	4 160	130	80	50 000	6
66081	LSS/4FT/TLEV/40W/40K/120-277/A1/STD	40	120-277	4 000	5 200	130	80	50 000	6







LED Shoplight



STANDARD's 4 foot LED Shoplight consumes at least 48 % less energy than it's traditional counterpart. It is equipped with a 5 foot cable with a direct plug-in and an ON/OFF pull chain.

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 (hrs)	Traditional equivalent (W) Fluo	Case qty (master)
65971	LSHOP/S2/40W/40K/120/ND/STD	40	120	4 000	4 000	80	54 000	2x32	4

05



Lumen values are derived from photometric testing
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com




LED Vapor tight



The LSV Vapor Tight series is an enclosed luminaire that combines state-of-the-art LED technology with an IP rated vapor tight housing. This luminaire is protected against extreme temperatures, the intrusion of dust and jets of waters projected from any direction. Its durable construction provides protection against harsh environmental conditions and corrosion.

- Impact resistant polycarbonate construction
- Integrated durable gasket that seals the entire enclosure
- UV stabilized lens

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Case qty (master)
65056	LSV/S2/40W/40K/2/DD1/FP/STD	40	120-277	4 000	5 200	82	80 000	6
65057	LSV/S2/40W/40K/3/DD1/FP/STD	40	347	4 000	5 200	82	80 000	6
65058	LSV/S2/60W/40K/2/DD1/FP/STD	60	120-277	4 000	7 800	82	80 000	6
Narrow								
66196	LSV/N/35W/40K/120-277/DD1/FP/A1/STD	40	120-277	4 000	4550	80 +	50 000	4
66197	LSV/N/40W/40K/120-277/DD1/FP/A1/STD	40	120-277	4 000	5200	80 +	50 000	4
66198	LSV/N/35W/40K/347/DD1/FP/A1/STD	40	347	4 000	4550	80 +	50 000	4
66199	LSV/N/52W/40K/347/DD1/FP/A1/STD	40	347	4 000	6760	80 +	50 000	4



Accessory

Order code	Description	Type
64187	FPV/LSV/STAINLESS/STEEL/CLIPS/STD	Steel clip



Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and DLC qualified products,
please visit www.standardpro.com
¹Estimated life hours




LED Tri-proof

The LSVS Tri-Proof series is highly resistant to heavy impacts (IK10), water jets (IP66), dust, and temperature variations. This luminaire balances high performance lighting while providing minimum glare.

05



Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Case qty (master)
2'								
64922	LSVS/20W/2FT/40K/2/ND/FP/L/STD	20	120-277	4 000	1 900	80	63 000	6
4'								
64923	LSVS/40W/4FT/40K/2/ND/FP/L/STD	40	120-277	4 000	3 800	80	63 000	6
64924	LSVS/40W/4FT/40K/3/ND/FP/L/STD	40	347	4 000	3 800	80	63 000	6




Accessory

Order code	Description	Type
64175	LSVS/ACC/AIRCAB/STD	Steel cables



Included in the box

Connectors for linkable mounting
Mounting clips: one set per luminaire
One 6 ft (183 cm) cable, with one set of connectors at each end





LED High Bay

With STANDARD's high bay line, it is now easy to modernize your commercial or industrial applications; it is the perfect alternative for your traditional lighting system.

Our high efficacy LED high bay luminaires provide premium performance, quality and versatility. With up to 60% lower power consumption compared to traditional fluorescent and HID light sources, these luminaires are designed to reduce your total cost of ownership, while providing modern uniform light. These luminaires are ideal for high ceilings (10' to 60') in warehouses, manufacturing facilities, gymnasiums, grocery stores or any other large indoor space, and they provide direct and semi-direct light.



LED Bell Shape

Our LED high bay bell shape luminaires are the perfect option in either new or retrofit solutions. Designed for high ceiling applications, this series of highly efficient LED luminaires and reflectors ensure proper light distribution for the needs of the space. The contractor approved hook design facilitates easy and fast installation and is a perfect choice in replacing existing traditional HID luminaires. This luminaire is wash down ready, dust tight and requires little to no maintenance.





120 V



347 V

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Case qty (master)
65785	LPHBB/100W/40K/2/DD1/STD	100	120-277	4 000	12 933	80	≥100 000	1
65787 ²	LPHBB/100W/50K/2/DD1/STD	100	120-277	5 000	13 249	80	≥100 000	1
65786 ²	LPHBB/100W/40K/3/DD1/STD	100	347-480	4 000	12 980	80	≥100 000	1
65788 ²	LPHBB/100W/50K/3/DD1/STD	100	347-480	5 000	13 124	80	≥100 000	1
65388	LPHBB/S3/150W/40K/2/DD1/FP/STD	150	120-277	4 000	19 323	80	≥87 000	1
65789 ²	LPHBB/S3/150W/50K/2/DD1/STD	150	120-277	5 000	18 617	80	≥87 000	1
65389	LPHBB/S3/150W/40K/3/DD1/FP/STD	150	347-480	4 000	19 323	80	≥87 000	1
65790 ²	LPHBB/S3/150W/50K/3/DD1/STD	150	347-480	5 000	18 851	80	≥87 000	1
65791	LPHBB/200W/40K/2/DD1/STD	200	120-277	4 000	26 062	80	≥72 000	1
65795 ²	LPHBB/200W/50K/2/DD1/STD	200	120-277	5 000	26 491	80	≥72 000	1
65796	LPHBB/200W/40K/3/DD1/STD	200	347-480	4 000	26 080	80	≥72 000	1
65797 ²	LPHBB/200W/50K/3/DD1/STD	200	347-480	5 000	26 385	80	≥72 000	1



Reflectors and Lens

Order code	Description	Type	Beam angle (°)
64201	LHBB/ALR60/STD	Reflector	60
64202	LHBB/ALR90/STD	Reflector	90
64203	LHBB/ACR70/STD	Reflector	70
66030	LPHBB/ACR60/22IN/STD	Reflector	60
66031	LPHBB/ACR/LENS/22IN/STD	Lens	-



Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and DLC qualified products,
please visit www.standardpro.com

¹Estimated life hours

²Non-stocked items, contact STANDARD for lead time and minimum order quantity






LED LHBE Eco


This series offers an economical and ecological solution for your high bay applications. With a linear, low profile and durable design, they provide mounting heights ranging from 10 to 50 feet. Take advantage of superior performance while reducing your energy consumption and maintenance costs with this economic solution.



Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Case qty (master)
2'								
65515	LHBE/S2/110W/2FT/40K/2/DD1/FP/STD	110	120-277	4 000	14 300	84	122 000	1
65516	LHBE/S2/162W/2FT/40K/2/DD1/FP/STD	162	120-277	4 000	21 060	84	122 000	1
65518	LHBE/S2/162W/2FT/50K/2/DD1/FP/STD	162	120-277	5 000	21 222	84	122 000	1
65561 ²	LHBE/S2/162W/2FT/40K/3/DD1/FP/STD	162	347	4 000	21 060	84	122 000	1
4'								
65517	LHBE/S2/223W/4FT/40K/2/DD1/FP/STD	223	120-277	4 000	28 990	84	122 000	1
65519	LHBE/S2/223W/4FT/50K/2/DD1/FP/STD	223	120-277	5 000	29 213	84	122 000	1
65559	LHBE/321W/4FT/50K/2/DD1/FP/STD	321	120-277	5 000	42 051	84	122 000	1
65562 ²	LHBE/S2/223W/4FT/40K/3/DD1/FP/STD	223	347	4 000	28 990	84	122 000	1
65560 ²	LHBE/321W/4FT/50K/3/DD1/FP/STD	321	347	5 000	42 051	84	122 000	1



2'



4'

Accessories

Order code	Description	Type	Compatible with
64614	LHBE/ACC/110W-220W/VHOOKCHAIN/STD	Hanger kit	65515, 65517, 65519, 65559, 65560, 65562
64615	LHBE/ACC/110W/VHOOKCHAIN/STD	Hanger kit	65516, 65518, 65561
64616	LHBE/ACC/PENDANTMOUNT/STD	Pendant mount	65515, 65516, 65517, 65518, 65519, 65559
64617	LHBE/ACC/110W/WG/STD	Wireguard	65515
64618	LHBE/ACC/160W/WG/STD	Wireguard	65516, 65518, 65561
64619	LHBE/ACC/220W/WG/STD	Wireguard	65517, 65519, 65562
64620	LHBE/ACC/110W-220W/SMK/STD	Surface mount	65515, 65517, 65519, 65562
64621	LHBE/ACC/160W/SMK/STD	Surface mount	65515, 65518, 65559, 65560, 65561



Lumen values are derived from photometric testing
 For a complete list of compatible dimmers and DLC qualified products, please visit www.standardpro.com
¹Estimated life hours
²Stepdown transformer included



DAMP



DIMMABLE



5 YEARS WARRANTY



UL US



DLC PREMIUM





LED Outdoor

STANDARD offers a wide range of LED outdoor luminaires that are perfect for a large variety of applications which create a visual impact for your building. Whether you need to light up a pathway, entryway, parking area or enhance architectural features, you are sure to find the perfect lighting solution for your needs!

LED Wall Pack

STANDARD's wide variety of Wall Pack luminaires is perfect for many applications such as office buildings, entryways, schools or parking areas. They are offered in different housing colours and wattages to create a seamless look with your environment.

- The full cutoff wall packs in 3 000 K are IDA (International - Dark Sky Association) approved
- 0-10 V dimming on dimmable models




Classic 30 W




Classic 40, 50, 60, 120 W


Order code	Description	Watts	Volts	Colour temp.	CRI	Life L70	Lumen output	Finish	Dimming capability	Traditionnal equivalent (W)		Case qty
		(W)	(VAC)	(K)		(hrs)	(lm)		(Yes/No)	MH	HPS	(master)
Classic Wall Packs												
65579	LWP/CLASSIC/S2/30W/40K/120-277V/BRZ/STD	30	120-277	4 000	≥70	50 000	2 778	Bronze	No	100	70	4
65582	LWP/CLASSIC/S2/40W/40K/347V/BRZ/STD	40	277-480	4 000	≥70	50 000	4 654	Bronze	No	175	100	1
65580	LWP/CLASSIC/S2/50W/40K/120-277V/BRZ/STD	50	120-277	4 000	≥70	50 000	5 110	Bronze	Yes	175	150	1
65581	LWP/CLASSIC/S2/60W/40K/120-277V/BRZ/STD	60	120-277	4 000	≥70	50 000	7 456	Bronze	Yes	250	200	1
66042	LWP/CLASSIC/S2/60W/40K/347/BRZ/STD	60	277-480	4 000	≥70	50 000	6 673	Bronze	Yes	250	200	1
66043	LWP/CLASSIC/120W/40K/120-277/BRZ/STD	120	120-277	4 000	≥70	50 000	11 683	Bronze	Yes	400	250	1



Classic 30 W



Classic 40, 50, 60 W



Classic 120 W

Integrated Dusk to Dawn photocell
to maximize energy efficiency




Full Cutoff




Square

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Finish	Dimming capability (Yes/No)	Traditionnal equivalent (W)		Case qty (master)
										MH	HPS	
Full Cutoff Wall Packs												
65565 ²	LWP/FCO/50W/30K/120-277/BRZ/STD	50	120-277	3 000	≥80	50 000	5 617	Bronze	No	175	150	1
65566	LWP/FCO/50W/40K/120-277/BRZ/STD	50	120-277	4 000	≥80	50 000	5 826	Bronze	No	175	150	1
65567 ²	LWP/FCO/80W/30K/120-277/BRZ/STD	80	120-277	3 000	≥80	50 000	8 957	Bronze	Yes	250	200	1
65568	LWP/FCO/80W/40K/120-277/BRZ/STD	80	120-277	4 000	≥80	50 000	9 053	Bronze	Yes	250	200	1
Square Wall Pack												
65570 ¹	LWP/SQR/S2/20W/40K/120-277/BRZ/STD	20	120-277	4 000	≥80	50 000	2 100	Bronze	No	70	70	6



Full Cutoff




Square



Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and DLC qualified products, please visit www.standardpro.com

¹ CAUTION: This product uses an input 100-277 VAC driver, the actual working voltage is dependent on the input voltage of the photocell that is installed on the product (where applicable)




Integrated Dusk to Dawn photocell
to maximize energy efficiency




Sleek

Order code	Description	Watts	Volts	Colour temp.	CRI	Life L70	Lumen output	Finish	Traditionnal equivalent (W)		Case qty
		(W)	(VAC)	(K)		(hrs)	(lm)		MH	HPS	(master)
63771	LED/WP/18W/40K/120V/WH/PC/STD	18	120	4 000	≥80	50 000	1 750	White	70	50	12
63772	LED/WP/18W/40K/120V/BLK/PC/STD	18	120	4 000	≥80	50 000	1 750	Black	70	50	12
63773	LED/WP/18W/40K/120V/SLV/PC/STD	18	120	4 000	≥80	50 000	1 750	Silver	70	50	12
63774	LED/WP/18W/40K/120V/BRZ/PC/STD	18	120	4 000	≥80	50 000	1 750	Bronze	70	50	12
63775	LED/WP/30W/40K/120V/WH/PC/STD	30	120	4 000	≥80	50 000	2 800	White	100	70	12
63776	LED/WP/30W/40K/120V/BLK/PC/STD	30	120	4 000	≥80	50 000	2 800	Black	100	70	12
63777	LED/WP/30W/40K/120V/SLV/PC/STD	30	120	4 000	≥80	50 000	2 800	Silver	100	70	12
63778	LED/WP/30W/40K/120V/BRZ/PC/STD	30	120	4 000	≥80	50 000	2 800	Bronze	100	70	12



Sleek 18 W



Sleek 30 W


Lumen values are derived from photometric testing
For a complete list of compatible dimmers, please visit www.standardpro.com
CAUTION: These product use an input 100-277 VAC driver, the actual working voltage is dependent on the input voltage of the photocell that is installed on the product (where applicable)




LED Slim Wall Pack

Slim wall pack luminaires offer a sleek design with adjustable tilt to ensure light is being directed where needed. They are perfect for a variety of applications such as entrances, walkways or building perimeters in residential or commercial applications.


- Adjustable tilt up to 90°
- 0-10 V dimming on some models



12 W




30, 40, 50 W




80 W


Order code	Description	Watts	Volts	Colour temp.	CRI	Life L70	Lumen output	Finish	Dimming capability	Traditionnal equivalent (W)		Case qty
		(W)	(VAC)	(K)		(hrs)	(lm)		(Yes/No)	MH	HPS	(master)
65571	LWP/SLM/S2/12W/40K/120-277/BRZ/STD	12	120-277	4 000	≥80	50 000	1 324	Bronze	No	50	-	8
65572	LWP/SLM/S2/30W/40K/120-277/BRZ/STD	30	120-277	4 000	≥80	50 000	3 337	Bronze	No	100	100	4
65573	LWP/SLM/S2/30W/40K/120-277/WH/STD	30	120-277	4 000	≥80	50 000	3 337	White	No	100	100	4
65578	LWP/SLM/S2/40W/40K/347/BRZ/STD	40	347-480	4 000	≥80	50 000	4 204	Bronze	Yes	150	100	4
65574	LWP/SLM/S2/50W/40K/120-277/BRZ/STD	50	120-277	4 000	≥80	50 000	5 349	Bronze	No	175	150	4
65575	LWP/SLM/S2/50W/40K/120-277/WH/STD	50	120-277	4 000	≥80	50 000	5 349	White	No	175	150	4
65576	LWP/SLM/S2/80W/40K/120-277/BRZ/STD	80	120-277	4 000	≥80	50 000	9 328	Bronze	Yes	250	200	2
65577	LWP/SLM/S2/80W/40K/120-277/WH/STD	80	120-277	4 000	≥80	50 000	9 328	White	Yes	250	200	2



12 W



30, 40, 50 W



80 W

ADJUSTABLE
WALL PACK

RATING



WET



TEMPERATURE



WARRANTY



Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and DLC qualified products,
please visit www.standardpro.com




LED Flood

Flood luminaires are perfect for various applications such as wall washing, lighting pathways, landscape or signage lighting. They are offered in multiple wattages to fit both residential and commercial uses, and have a wide flood distribution for a large and uniform light pattern.




Yoke 30, 50 W

Order code	Description	Watts	Volts	Colour temp.	CRI	Life L70	Lumen output	Finish	NEMA type	Traditional equivalent (W)		Case qty
		(W)	(VAC)	(K)		(hrs)	(lm)			MH	HPS	(master)
65591	LFL/S2/30W/40K/YK/120-277/BRZ/STD	30	120-277	4 000	≥80	50 000	3 400	Bronze	7H x 7V	100	70	6
65593	LFL/S2/50W/40K/YK/120-277/BRZ/STD	50	120-277	4 000	≥80	50 000	6 000	Bronze	7H x 7V	175	150	6



Yoke 30 W



Yoke 50 W



Knuckle 10 W




Knuckle 12 W




Knuckle 30, 50 W


Order code	Description	Watts	Volts	Colour temp.	CRI	Life L70	Lumen output	Finish	NEMA type	Traditionnal equivalent (W)		Case qty
		(W)	(VAC)	(K)		(hrs)	(lm)			MH	HPS	(master)
63323	LED/FL/10W/30K/KN/120-277V/BRZ/STD	10	120-277	3 000	≥70	50 000	900	Bronze	-	50	35	8
64217	LED/FL/10W/30K/KN/120-277V/WH/STD	10	120-277	3 000	≥70	50 000	900	White	-	50	35	8
64218	LED/FL/10W/30K/KN/120-277V/BLK/STD	10	120-277	3 000	≥70	50 000	900	Black	-	50	35	8
64219	LED/FL/10W/40K/KN/120-277V/WH/STD	10	120-277	4 000	≥70	50 000	900	White	-	50	35	8
65586	LFL/S2/12W/40K/KN/120-277/BRZ/STD	12	120-277	4 000	≥80	50 000	1 400	Bronze	7H x 6V	50	35	12
65588	LFL/S2/12W/40K/KN/120-277/BLK/STD	12	120-277	4 000	≥80	50 000	1 400	Black	7H x 6V	50	35	12
65590	LFL/S2/30W/30K/KN/120-277/BRZ/STD	30	120-277	3 000	≥80	50 000	3 200	Bronze	7H x 7V	100	70	6
65589	LFL/S2/30W/40K/KN/120-277/BRZ/STD	30	120-277	4 000	≥80	50 000	3 400	Bronze	7H x 7V	100	70	6
65592	LFL/S2/50W/40K/KN/120-277/BRZ/STD	50	120-277	4 000	≥80	50 000	6 000	Bronze	7H x 7V	175	150	6




Knuckle 10 W



Knuckle 12 W



Knuckle 30 W



Knuckle 50 W

Accessories

Order code	Description	Type	Finish	Compatible with
64150 ¹	KN/ACC/WPCOVER/BRZ/STD	Weather proof cover plate	Bronze	63323, 65586, 65589, 65590, 65592
64208 ¹	KN/ACC/WPCOVER/WH/STD	Weather proof cover plate	White	64217, 64219
64209 ¹	KN/ACC/WPCOVER/BLK/STD	Weather proof cover plate	Black	64218, 65588



RATING



NON-DIMMABLE



WET



TEMPERATURE



WARRANTY



Lumen values are derived from photometric testing.
For a complete list of DLC qualified products, please visit www.standardpro.com
¹ 2 screws (10/24") and foam plate included with weather proof cover plate

LED Large Flood and Area



Slip Fitter
100, 150 W



Slip Fitter
220 W



Slip Fitter
380 W



Straight Arm
100, 150 W



Straight Arm
220 W



Yoke 100, 150 W



Yoke 220 W



Yoke 380 W

Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Finish	NEMA type	Distribution type	Traditionnal equivalent (W) MH HPS	Case qty (master)
------------	-------------	-----------	-------------	------------------	-----	----------------	-------------------	--------	-----------	-------------------	------------------------------------	-------------------

Slip Fitter

65594 ¹	LFL/L/S2/100W/40K/III/SF/120-277/BRZ/STD	100	120-277	4 000	≥80	50 000	12 468	Bronze	7H x 6V	III	250 200	1
65596 ¹	LFL/L/S2/150W/40K/III/SF/120-277/BRZ/STD	150	120-277	4 000	≥80	50 000	18 852	Bronze	7H x 6V	III	400 250	1
65601 ¹	LFL/L/S2/150W/40K/III/SF/347/BRZ/STD	150	277-480	4 000	≥80	50 000	18 383	Bronze	7H x 6V	III	400 250	1
65597 ¹	LFL/L/S2/220W/40K/III/SF/120-277/BRZ/STD	220	120-277	4 000	≥80	50 000	28 362	Bronze	7H x 6V	III	400 400	1
65602 ¹	LFL/L/S2/220W/40K/III/SF/347/BRZ/STD	220	277-480	4 000	≥80	50 000	27 252	Bronze	7H x 6V	III	400 400	1
66037 ¹	LFL/XL/380W/40K/II/SF/347/BRZ/STD	380	277-480	4 000	≥80	50 000	43 365	Bronze	7H x 7V	II	1 000 1 000	1

Straight Arm

66060	LFL/L/S2/100W/40K/III/MA/120-277/BRZ/STD	100	120-277	4 000	≥80	50 000	12 468	Bronze	7H x 6V	III	250 200	1
66066	LFL/L/S2/150W/40K/III/MA/120-277/BRZ/STD	150	120-277	4 000	≥80	50 000	18 852	Bronze	7H x 6V	III	400 250	1
66072	LFL/L/S2/220W/40K/III/MA/120-277/BRZ/STD	220	120-277	4 000	≥80	50 000	28 362	Bronze	7H x 6V	III	400 400	1

Yoke

66059	LFL/L/S2/100W/40K/II/YK/120-277/BRZ/STD	100	120-277	4 000	≥80	50 000	12 105	Bronze	7H x 6V	II	250 200	1
66065	LFL/L/S2/150W/40K/II/YK/120-277/BRZ/STD	150	120-277	4 000	≥80	50 000	18 486	Bronze	7H x 6V	II	400 250	1
66068	LFL/L/S2/150W/40K/II/YK/347/BRZ/STD	150	277-480	4 000	≥80	50 000	17 972	Bronze	7H x 6V	II	400 250	1
66071	LFL/L/S2/220W/40K/II/YK/120-277/BRZ/STD	220	120-277	4 000	≥80	50 000	26 219	Bronze	7H x 6V	II	400 400	1
66078	LFL/L/S2/220W/40K/II/YK/347/BRZ/STD	220	277-480	4 000	≥80	50 000	27 582	Bronze	7H x 6V	II	400 400	1
66036	LFL/XL/380W/40K/II/YK/347/BRZ/STD	380	277-480	4 000	≥80	50 000	43 365	Bronze	7H x 7V	II	1 000 1 000	1

Accessory

Order code	Description	Type	Finish	Compatible with
66155	LFL/L/S2/ACC/SF/WALL MOUNT/STD	Slip fitter to wall mount	Bronze	65594, 65596, 65601, 65597, 65602, 66037



DIMMABLE

IP65
RATING

WET




TEMPERATURE


5 YEARS
WARRANTY

Lumen values are derived from photometric testing
For a complete list of compatible dimmers and DLC qualified products,
please visit www.standardpro.com
*Use a post with a diameter of 2 3/8"


Dimensions




Slip Fitter 100, 150 W




Slip Fitter 220 W




Slip Fitter 380 W




Straight Arm 100, 150 W




Straight Arm 220 W



Yoke 100, 150 W



Yoke 220 W





Yoke 380 W



LED Yard Light



Integrated Dusk to Dawn photocell to maximize energy efficiency



Order code	Description	Watts	Volts	Colour temp.	CRI	Life L70	Lumen output	Finish	Beam angle	Distribution type	Traditionnal equivalent (W)		Case qty
		(W)	(VAC)	(K)		(hrs)	(lm)		(°)		MH	HPS	(master)
65569	LYL/S2/50W/40K/120-277/SLV/STD	50	120-277	4 000	≥80	50 000	5 500	Silver	120	V	150	100	2



Lumen values are derived from photometric testing
For a complete list of DLC qualified products, please visit www.standardpro.com
CAUTION: This product uses an input 100-277 VAC driver, the actual working voltage is dependent on the input voltage of the photocell that is installed on the product (where applicable)


STANDARD © 2017 STANDARD Products Inc. All Rights Reserved.
www.standardpro.com Rev. January 11, 2018.



LED Bollard

LED outdoor bollards are perfect for lighting pathways and entryways. They will fit seamlessly into the landscape and add a decorative touch to your building. They will also provide adequate lighting for increased safety on your property.

- Offered in two diffuser styles
- Cone allows for a larger lumen output
- Louver replicates the traditional look



Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Finish	Distribution type	Traditionnal equivalent (W) MH	Case qty (master)
Louver											
65530	LBOL8/LOUV/25W/40K/120-277/RND/BRZ/STD	25	120-277	4 000	≥70	50 000	1 325	Bronze	V	50/70	1
Cone											
65531	LBOL8/CONE/25W/40K/120-277/RND/BRZ/STD	25	120-277	4 000	≥70	50 000	1 925	Bronze	V	50/70	1

Lumen values are derived from photometric testing





LED Canopy

With its superior rugged construction and low profile design, the LKAN series of luminaires is the perfect solution for parking garages and canopy applications. Wet location certified with an IP65 rating, this luminaire is dust and moisture proof, ideal for installation in areas susceptible to dirt and dust.



Mounting plate attached with a clip in order to free up your hands for wiring!

Order code	Description	Watts (W)	Volts (V)	Colour temp. (K)	Lumen output (lm)	CRI	Life L70 ¹ (hrs)	Distribution type	Case qty (master)
64841	LKAN/45W/40K/120-277V/BRZ/CL/STD	45	120-277	4 000	4 130	70	50 000	V	6
64842	LKAN/45W/40K/347V/BRZ/CL/STD	45	347	4 000	4 101	70	50 000	V	6
64843	LKAN/65W/40K/120-277V/BRZ/CL/STD	65	120-277	4 000	6 458	70	50 000	V	6
64844	LKAN/65W/40K/347V/BRZ/CL/STD	65	347	4 000	6 532	70	50 000	V	6



Order code	Description	Replacement
66237	LKAN/ACC/LENS/CL/STD	64841, 64842, 64843, 64844



DIMMABLE



RATING



WET



TEMPERATURE



WARRANTY



Lumen values are derived from photometric testing
For a complete list of compatible dimmers and DLC qualified products, please visit www.standardpro.com
¹Estimated life hours

LED Security Light


LED security lights are perfect for applications such as yards, walkways, driveways, patios, parking lots and loading areas. They can easily replace traditional luminaires while offering superior performance and savings on energy consumption.

The security lights are equipped with a motion sensor allowing you to set the lights to turn ON when motion is detected during daytime or nighttime. This ensures that the area is well lit and provides added security at night.

- 180° detection motion sensor
- Integrated Dusk to Dawn photocell
- Adjustable heads to direct the light where needed



Order code	Description	Watts	Volts	Colour temp.	CRI	Life L70	Lumen output	Finish	Beam angle	Traditionnal equivalent (W) MH	Case qty (master)
		(W)	(VAC)	(K)		(hrs)	(lm)		(°)		
64600	LED/SL2H/24W/30K/120-277V/MS/BRZ/STD	24	120-277	3 000	≥80	50 000	1 980	Bronze	60	50/70	4
64601	LED/SL2H/24W/30K/120-277V/MS/WH/STD	24	120-277	3 000	≥80	50 000	1 980	White	60	50/70	4
64602 ¹	LED/SL2H/24W/40K/120-277V/MS/BRZ/STD	24	120-277	4 000	≥80	50 000	2 058	Bronze	60	50/70	4
64603 ¹	LED/SL2H/24W/40K/120-277V/MS/WH/STD	24	120-277	4 000	≥80	50 000	2 058	White	60	50/70	4



RATING



NON-DIMMABLE



WET



TEMPERATURE



WARRANTY



Intertek



ENERGY STAR

Lumen values are derived from photometric testing
For a complete list of ENERGY STAR qualified products, please visit www.standardpro.com
CAUTION: These products use an input 100-277 VAC driver, the actual working voltage is dependent on the input voltage of the photocell that is installed on the product (where applicable)



Step Down Transformer

Convert high-voltage power to low-voltage power and allow 100-277 V LED drivers to operate on 347 V mains. It can be installed either in the junction box or directly on the luminaire.

Our transformers are protected by a vacuum varnish impregnation and bake process for superior noise attenuation and consistency of lighting in transformer applications.



Order code	Description	Style	Type	Input volts (V)	Output volts (V)	Max load (VA)	Frequency (Hz)	Weight (g)
64656	STPDN/NPLNT/60VA/347-240V/60Hz/AUTO/STD	Nipple-Mount	Auto Transformer	347	240	60	50/60	450
64657	STPDN/NPLNT/130VA/347-240V/60Hz/AUTO/STD	Nipple-Mount	Auto Transformer	347	240	130	50/60	700
64658	STPDN/NPLNT/165VA/347-240V/60Hz/AUTO/STD	Nipple-Mount	Auto Transformer	347	240	165	50/60	1 100
64659	STPDN/NPLNT/260VA/347-240V/60Hz/AUTO/STD	Nipple-Mount	Auto Transformer	347	240	260	50/60	1 450
64660	STPDN/NPLNT/300VA/347-240V/60Hz/AUTO/STD	Nipple-Mount	Auto Transformer	347	240	300	50/60	1 450



Compatibility List

Order code	Description	Max load (VA)	Step Down STANDARD code	Order code	Description	Max load (VA)	Step Down STANDARD code
LED Commercial Downlights				Veloce™ Downlights			
64972	LCR/DL6/18W/35K/2/DD1/STD	60	64656	64799	VELOCE8/MOD/F/38W/40K/70/SLV/STD	165	64658
64973	LCR/DL6/18W/40K/2/DD1/STD	60	64656	64792	VELOCE8/MOD/F/26W/35K/70/BLK/STD	130	64657
64974	LCR/DL6/27W/35K/2/DD1/STD	60	64656	64793	VELOCE8/MOD/F/26W/40K/70/BLK/STD	130	64657
64975	LCR/DL6/27W/40K/2/DD1/STD	60	64656	64801	VELOCE8/MOD/F/38W/40K/70/BLK/STD	165	64658
64976	LCR/DL8/18W/35K/2/DD1/STD	60	64656	64796	VELOCE8/MOD/F/26W/35K/70/WH/STD	130	64657
64977	LCR/DL8/18W/40K/2/DD1/STD	60	64656	64797	VELOCE8/MOD/F/26W/40K/70/WH/STD	130	64657
64978	LCR/DL8/27W/35K/2/DD1/STD	60	64656	64803	VELOCE8/MOD/F/38W/40K/70/WH/STD	165	64658
64979	LCR/DL8/27W/40K/2/DD1/STD	60	64656				
64980	LCR/DL8/40W/40K/2/DD1/STD	60	64656	Striplight			
64981	LCR/DL10/54W/40K/2/DD1/STD	60	64656	65034	LSS/2FT/20W/40K/120-277/STD	130	64657
				65035	LSS/4FT/41W/40K/120-277/STD	130	64657
				65036	LSS/8FT/78W/40K/120-277/STD	130	64657
Veloce™ Downlights				Outdoor			
64744	VELOCE4/MOD/13W/30K/45/SLV/STD	60	64656	63323	LED/FL/10W/30K/KN/120-277V/STD	60	64656
64745	VELOCE4/MOD/13W/35K/45/SLV/STD	60	64656	64217	LED/FL/10W/30K/KN/120-277V/WH/STD	60	64656
64746	VELOCE4/MOD/13W/40K/45/SLV/STD	60	64656	64218	LED/FL/10W/30K/KN/120-277V/BLK/STD	60	64656
64750	VELOCE4/MOD/13W/30K/45/BLK/STD	60	64656	64219	LED/FL/10W/40K/KN/120-277V/WH/STD	60	64656
64751	VELOCE4/MOD/13W/35K/45/BLK/STD	60	64656	65530	LBOL8/LOUV/25W/40K/120-277/RND/BRZ/STD	130	64657
64752	VELOCE4/MOD/13W/40K/45/BLK/STD	60	64656	65531	LBOL8/CONE/25W/40K/120-277/RND/BRZ/STD	130	64657
64756	VELOCE4/MOD/13W/30K/45/WH/STD	60	64656	65579	LWP/CLASSIC/S2/30W/40K/120-277V/BRZ/STD	60	64656
64757	VELOCE4/MOD/13W/35K/45/WH/STD	60	64656	65580	LWP/CLASSIC/S2/50W/40K/120-277V/BRZ/STD	130	64657
64758	VELOCE4/MOD/13W/40K/45/WH/STD	60	64656	65581	LWP/CLASSIC/S2/60W/40K/120-277V/BRZ/STD	130	64657
64747	VELOCE4/MOD/F/13W/30K/70/SLV/STD	60	64656	65565	LWP/FCO/50W/30K/120-277/BRZ/STD	60	64656
64748	VELOCE4/MOD/F/13W/35K/70/SLV/STD	60	64656	65566	LWP/FCO/50W/40K/120-277/BRZ/STD	60	64656
64749	VELOCE4/MOD/F/13W/40K/70/SLV/STD	60	64656	65567	LWP/FCO/80W/30K/120-277/BRZ/STD	130	64657
64753	VELOCE4/MOD/F/13W/30K/70/BLK/STD	60	64656	65568	LWP/FCO/80W/40K/120-277/BRZ/STD	130	64657
64754	VELOCE4/MOD/F/13W/35K/70/BLK/STD	60	64656	65570	LWP/SQR/S2/20W/40K/120-277/BRZ/STD	60	64656
64755	VELOCE4/MOD/F/13W/40K/70/BLK/STD	60	64656	65571	LWP/SLM/S2/12W/40K/120-277V/BRZ/STD	60	64656
64759	VELOCE4/MOD/F/13W/30K/70/WH/STD	60	64656	65572	LWP/SLM/S2/30W/40K/120-277/BRZ/STD	60	64656
64760	VELOCE4/MOD/F/13W/35K/70/WH/STD	60	64656	65573	LWP/SLM/S2/30W/40K/120-277/WH/STD	60	64656
64761	VELOCE4/MOD/F/13W/40K/70/WH/STD	60	64656	65574	LWP/SLM/S2/50W/40K/120-277/BRZ/STD	60	64656
64762	VELOCE6/MOD/18W/35K/45/SLV/STD	130	64657	65575	LWP/SLM/S2/50W/40K/120-277/WH/STD	60	64656
64763	VELOCE6/MOD/18W/40K/45/SLV/STD	130	64657	65576	LWP/SLM/S2/80W/40K/120-277/BRZ/STD	130	64657
64774	VELOCE6/MOD/26W/35K/45/SLV/STD	130	64657	65577	LWP/SLM/S2/80W/40K/120-277/WH/STD	130	64657
64775	VELOCE6/MOD/26W/40K/45/SLV/STD	130	64657	65583	LFL/S2/12W/30K/KN/120-277/BRZ/STD	60	64656
64766	VELOCE6/MOD/18W/35K/45/BLK/STD	130	64657	65584	LFL/S2/12W/30K/KN/120-277/WH/STD	60	64656
64767	VELOCE6/MOD/18W/40K/45/BLK/STD	130	64657	65585	LFL/S2/12W/30K/KN/120-277/BLK/STD	60	64656
64778	VELOCE6/MOD/26W/35K/45/BLK/STD	130	64657	65586	LFL/S2/12W/40K/KN/120-277/BRZ/STD	60	64656
64779	VELOCE6/MOD/26W/40K/45/BLK/STD	130	64657	65587	LFL/S2/12W/40K/KN/120-277/WH/STD	60	64656
64770	VELOCE6/MOD/18W/35K/45/WH/STD	130	64657	65588	LFL/S2/12W/40K/KN/120-277/BLK/STD	60	64656
64771	VELOCE6/MOD/18W/40K/45/WH/STD	130	64657	65591	LFL/S2/30W/40K/YK/120-277/BRZ/STD	60	64656
64782	VELOCE6/MOD/26W/35K/45/WH/STD	130	64657	65590	LFL/S2/30W/30K/KN/120-277/BRZ/STD	60	64656
64783	VELOCE6/MOD/26W/40K/45/WH/STD	130	64657	65589	LFL/S2/30W/40K/KN/120-277/BRZ/STD	60	64656
64764	VELOCE6/MOD/F/18W/35K/70/SLV/STD	130	64657	65593	LFL/S2/50W/40K/YK/120-277/BRZ/STD	60	64656
64765	VELOCE6/MOD/F/18W/40K/70/SLV/STD	130	64657	65592	LFL/S2/50W/40K/KN/120-277/BRZ/STD	60	64656
64776	VELOCE6/MOD/F/26W/35K/70/SLV/STD	130	64657	65594	LFL/L/S2/100W/40K/III/SF/120-277/BRZ/STD	165	64658
64777	VELOCE6/MOD/F/26W/40K/70/SLV/STD	130	64657	66060	LFL/L/S2/100W/40K/III/MA/120-277/BRZ/STD	165	64658
64768	VELOCE6/MOD/F/18W/35K/70/BLK/STD	130	64657	66059	LFL/L/S2/100W/40K/II/YK/120-277/BRZ/STD	165	64658
64769	VELOCE6/MOD/F/18W/40K/70/BLK/STD	130	64657	65596	LFL/L/S2/150W/40K/III/SF/120-277/BRZ/STD	260	64659
64780	VELOCE6/MOD/F/26W/35K/70/BLK/STD	130	64657	66066	LFL/L/S2/150W/40K/III/MA/120-277/BRZ/STD	260	64659
64781	VELOCE6/MOD/F/26W/40K/70/BLK/STD	130	64657	66065	LFL/L/S2/150W/40K/II/YK/120-277/BRZ/STD	260	64659
64772	VELOCE6/MOD/F/18W/35K/70/WH/STD	130	64657	65597	LFL/L/S2/220W/40K/III/SF/120-277/BRZ/STD	300	64660
64773	VELOCE6/MOD/F/18W/40K/70/WH/STD	130	64657	66072	LFL/L/S2/220W/40K/III/MA/120-277/BRZ/STD	300	64660
64784	VELOCE6/MOD/F/26W/35K/70/WH/STD	130	64657	66071	LFL/L/S2/220W/40K/II/YK/120-277/BRZ/STD	300	64660
64785	VELOCE6/MOD/F/26W/40K/70/WH/STD	130	64657	65569	LYL/S2/50W/40K/120-277/SLV/STD	130	64657
64786	VELOCE8/MOD/26W/35K/45/SLV/STD	130	64657				
64787	VELOCE8/MOD/26W/40K/45/SLV/STD	130	64657				
64798	VELOCE8/MOD/38W/40K/45/SLV/STD	165	64658				
64790	VELOCE8/MOD/26W/35K/45/BLK/STD	130	64657				
64791	VELOCE8/MOD/26W/40K/45/BLK/STD	130	64657				
64800	VELOCE8/MOD/38W/40K/45/BLK/STD	165	64658				
64794	VELOCE8/MOD/26W/35K/45/WH/STD	130	64657				
64795	VELOCE8/MOD/26W/40K/45/WH/STD	130	64657				
64802	VELOCE8/MOD/38W/40K/45/WH/STD	165	64658				
64788	VELOCE8/MOD/F/26W/35K/70/SLV/STD	130	64657				
64789	VELOCE8/MOD/F/26W/40K/70/SLV/STD	130	64657				



Standard
Products



Standard
Products Inc



StandardProInc



Standardproducts



STANDARD
Products Inc



Standard
Products Inc



STANDARD
Products Inc

www.standardpro.com



Printed in Canada. © 2017 STANDARD Products Inc. All Rights Reserved.
Subject to change without notice. For the latest version, please refer to our website.
Rev. January 11, 2018

STANDARD[®]