






Projection		Scale	Free	DATE	10-19-2026
Drawing No.	VHK2AR-01S-01S				

VHK2AR-01S-01S

フィンガバルブ 難燃タイプ/1(P)・2(A)－おねじ

3D ビュー

[Click here in Adobe Acrobat to activate the interactive 3D View.](#)



VHK2AR-01S-01S

フィンガバルブ 難燃タイプ/1(P)・2(A)ーおねじ

図面

GUI ()	VHK*AR-01S-01S
VALVE (バルブ型式)	(2) 2ポート弁
COLOR (ツマミの色)	(-) グレー
BRACKET (ブラケット)	(-) なし
RP (接続ねじ R)	1/8
RA (接続ねじ R)	1/8
H ()	18
L1 ()	41
L2 ()	65.2
L3 ()	32.6
L4 ()	32.6
L5 ()	16.5
L6 ()	3.5
Q ()	11
B ()	57
BA (ブラケット アセンブリ品番)	VHK-B1A
S (六角対辺)	13
T (六角対辺)	13
C ()	44.5
D ()	14.5
E ()	1
F ()	27
G ()	22
J ()	16.5
K ()	26