



Claridge®

## Contract Furniture & Interiors

---


CATALOG 2019



# Claridge

The Writing Surface Experts®

A dry erase whiteboard's effectiveness as a communication tool is only as good as its writing surface, which is the primary medium for exchanging visual information. Not all writing surfaces are equal, and the quality and composition of the material used to make them directly affect the user experience.



Frameless Claridge Glass Whiteboard




Profile Series LCS<sup>3</sup> Porcelain® Whiteboard

## Table of Contents

3	Glass Whiteboards - Magnetic, Non-Magnetic, Non -Glare	16	Evolve Whiteboards and Tackboards
4	PROFILE SERIES LCS <sup>3</sup> Porcelain® Whiteboards	17	Evolve Sliding Systems
5	MIX Contemporary Whiteboards	18	Sliding Board Systems - Horizontal and Vertical
6	MIX Industrial Whiteboards	19	TrakIt Sliding Systems
7	MIX Contemporary Mobiles	20	Xchange and Envision Boards
8	MIX Industrial Mobiles	21	Tack Walls
9	MIX Biophilic Panels	22	Glass Marker Walls
10	X2 Mobiles	23	Porcelain Marker Walls
11	Space Creators	24	Sliding Glass Wall Systems
12	Concept Whiteboards	25	Sliding Porcelain Wall Systems
13	X2 Whiteboards and Tackboards	26	Accessories
14	Motif Whiteboard, Tackboard	27	Glass and Porcelain Colors
15	X2 Modular Boards	28	Materials and Finishes
		29	Finishes and Colors

# GLASS WHITEBOARDS Magnetic | Non-Magnetic | Non-Glare



Invisi-mount (MGMI)

## Stylish, functional and easy to maintain glass surface


- Silky smooth surface writes easily, erases cleanly – no ghosting
- 1/4" Tempered low-iron content glass for exceptional clarity
- Select from mounting methods
  - Invisi-mount – no visible hardware; gives the appearance of a floating panel
  - Stand-off Edge or Through Glass Mount – attractive stainless steel finish
- Available in sizes up to 5' x 10'
- Custom logos, custom colors and custom sizes available

## MAGNETIC


- Steel-backed glass doubles as a "tack" surface; furnished with rare earth magnets

## NON-GLARE


- Satin, velvety surface provides minimal distractions from glare and reflections



Invisi-Mount



Standoff Edge Mount



Standoff Through Glass Mount

*Magnetic accessories on page 26; Standard color options on page 27*




# PROFILE SERIES LCS<sup>3</sup> Porcelain® Frameless Whiteboards




LCS<sup>3</sup> Porcelain®

A cost effective alternative to frameless glass whiteboards

- Projection friendly, smooth writing surface writes easily, erases cleanly – no ghosting
- Available in dry erase whiteboard or chalkboard options
- Select from mounting methods
  - Invisi-mount – no visible hardware; gives the appearance of a floating panel
  - Stand-off Edge Mount – attractive stainless steel finish
- Available in sizes up to 5' x 10'
- Lifetime warranty



Invisi-Mount



Standoff Edge Mount

*Standard color options on page 27*



# MIX CONTEMPORARY WHITEBOARD



MIX Contemporary Wall-Mounted Whiteboards are companions to the Contemporary Mobiles

- Available in Claridge Glass and LCS<sup>3</sup> Porcelain<sup>®</sup> writing surfaces or Claridge Cork tack surface
- Metal accent strip highlights the integrated marker rail available in 180 optional powder coat colors
- Responsibly harvested Ash wood frame available in Clear, Vellum, Driftwood, and Rustic stains



**Standard Nominal Sizes:**

3' x 4', 3' x 5', 4' x 3', 4' x 4', 4' x 6', 4' x 8'

*Standard color options on page 29*



# MIX INDUSTRIAL WHITEBOARD



MIX Industrial Wall-Mounted Whiteboards are companions to the Industrial Mobiles

- Available in Claridge Glass and LCS<sup>3</sup> Porcelain<sup>®</sup> writing surfaces or Claridge Cork tack surface
- Metal accent strip highlights the integrated marker rail available in matte black finish, or your choice of 180 optional powder coat colors
- Responsibly harvested Ash wood frame available in Clear, Vellum, Driftwood, and Rustic stains
- Metal corner accents with exposed hex bolts in matte clear finish



**Standard Nominal Sizes:**

3' x 4', 3' x 5', 4' x 3', 4' x 4', 4' x 6', 4' x 8'

*Standard color options on page 29*



# MIX CONTEMPORARY MOBILE



- Responsibly harvested Ash wood frames available in Clear, Vellum, Driftwood and Rustic stains
- Metal bases and accent strips available in Signal White, Slate Gray or Matte Black with 180 optional powder coat colors
- Mobiles come with hubless casters
- Partial and full height mobiles measure 72" from top to bottom, in panel widths ranging from 36" to 72"



## Standard Nominal Sizes:

Partial (HxW)	Full (HxW)
48" x 36"	60" x 36"
36" x 48"	60" x 42"
48" x 48"	60" x 48"
48" x 60"	*60" x 60"
*48" x 72"	

\*Glass and Claridge Cork availability limited in these larger sizes.

Standard color options on page 29



# MIX INDUSTRIAL MOBILE



- Responsibly harvested Ash wood frames available in Clear, Vellum, Driftwood and Rustic stains
- Metal base is finished with a clear powder coating that retains the industrial flair and protects against rust and scratches
- Industrial casters include exposed brake locks
- Partial and full height mobiles measure 72" from top to bottom, in panel widths ranging from 36" to 72" (72" width is available for partial height only)



## Standard Nominal Sizes:

Partial (HxW)	Full (HxW)
48" x 36"	60" x 36"
36" x 48"	60" x 42"
48" x 48"	60" x 48"
48" x 60"	*60" x 60"
*48" x 72"	

\*Glass and Claridge Cork availability limited in these larger sizes.

Standard color options on page 29



# MIX BIOPHILIC PANEL



- Available on Contemporary or Industrial mobiles
- Choose from 2 designs - Om and Serenity, custom designs available upon request
- Responsibly harvested Ash wood frame available in Clear, Vellum, Driftwood, and Rustic stains
- Available on full height mobiles measuring 72" from top to bottom, in panel width of 42"
- Numerous credit contributions for LEED® v4 projects (BD+C, ED+C, O+M)
- Wall garden installations have significant noise reduction coefficient (Nrc)



Serenity



Om

## Standard Industrial Metal Colors

Metal Base: Matte Clear  
Accent Strip: Matte Black

## Standard Contemporary Metal Colors

Metal Base and Accent Strip: White, Gray & Matte Black

*Standard color options on page 29*



# X2 MOBILES



## Double Sided Mobile Whiteboards

- Available with any combination of whiteboard, tackboard and/or glass
- Mobiles are 72" high
- Whiteboard/Tackboard mobiles available in four widths: 30", 36", 48", and 60"
- Glass mobiles available in widths up to 42"
- Custom sizes available
- Full height, open or tackable panel at the bottom
- Locking casters
- Optional ganging mechanism


## 3-Caster Mobile

- Position between workstations
- Designed for mobility in tight spaces

## A-Frame Mobile

A-frame integrates aesthetics with flexibility – a writing surface, a divider, an announcement board.

- Full-length LCS<sup>3</sup> Porcelain® whiteboard surface both sides
- Black Powder Coat finish aluminum frame
- Display rail with hooks for flip charts/sketch pads
- Locking casters




3-Caster Mobile




Combo Board

# SPACE CREATORS



- A functional, movable environment that can be reconfigured at a moment's notice
- Carve out privacy for touchdown spaces and personalize the look to meet individual needs
- Stand alone or group together; simple ganging mechanism included
- Select from one to four tiles
- Panels extend fully to the floor for complete privacy
- Low profile foot provides stability

Customize panel size, material and color to satisfy specific requirements. Panels can be whiteboard or tackboard.



Unlimited configurations



# ALUMINUM TRIM Whiteboards and Tackboards



## CONCEPT WHITEBOARDS

Concept features a narrow aluminum trim profile with eased edge. Available with marker or tack board.

When longer lengths are required, ask about *Concept Connected*; boards are joined on site with a narrow H-bar connector.

- Whiteboards – Projection friendly Low Gloss White LCS<sup>3</sup> Porcelain<sup>®</sup> enamel steel
- Tackboards – Carnegie, Guilford or Maharam fabrics, Claridge Cork or COM
- Aluminum frames in Satin Anodize finish or Powder Coat finish


Concept trim



Concept whiteboard tray (standard)



# ALUMINUM TRIM Whiteboards and Tackboards




Optional fixed accessory tray

## X2 WHITEBOARDS AND TACKBOARDS

X2 Whiteboard's clean lines fit the design requirements of virtually any space. Available in LCS<sup>3</sup> Porcelain®, Claridge Glass whiteboards, and tackboards with minimal aluminum trim.

- Satin anodized trim can be powder coated in 24 standard colors, 180 optional colors and unlimited custom colors
- Available with fixed marker tray or optional magnetic tray




No reveal

With reveal



Optional magnetic tray



# WOOD TRIM Whiteboards and Tackboards



## MOTIF BOARDS

**Motif** has rounded edge profile with a narrow face trim. Available with marker or tack board

- Whiteboards – Projection friendly Low Gloss White LCS<sup>3</sup> Porcelain® enamel steel
- Tackboards – Carnegie, Guilford or Maharam Fabrics, Claridge Cork or COM
- Custom finishes available

## Wood Finish Options

*Colors are produced with reasonable accuracy.*



Maple

Mahogany


Cherry

Walnut

Espresso

Ebony

Motif trim



# MODULAR BOARDS




## X2 MODULAR BOARDS

Modular Communication System boards provide writing and tack surfaces that perform and look great at the same time, allowing users to create a mosaic of functional artwork on the wall.

- Sizes from 18" x 24" to 4' x 8'
- Available in LCS<sup>3</sup> Porcelain® enamel steel, magnetic glass, cork and fabric
- Hang portrait or landscape
- Assemble individually or as groupings
- Patterns and colors to coordinate or complement room décor



Sample configurations



# EVOLVE WHITEBOARDS AND TACKBOARDS




Evolve Whiteboards and Tackboards blend a wide trim at top and bottom with a narrow trim along sides for unique design appeal.

- LCS<sup>3</sup> Porcelain® enamel steel writing surface in projection-friendly low gloss white
- Tackboards available in Guilford, Carnegie, Maharam, Claridge Cork or COM
- Whiteboards available in 4' and 5' heights, in widths up to 16'.
- Snap-on tray can be easily added or removed




Wide top/narrow edge



Accessory tray



# EVOLVE SLIDING SYSTEM



Evolve whiteboards are on the move. Sliding board can be added to a fixed wallboard to increase usable surfaces or to conceal/reveal information written on the board surface.

- Fixed whiteboard panel in sizes up to 4' x 8' and sliding panels in 3' and 4' widths
- Sliding panel moves smoothly on top and bottom rollers
- Snap-on tray furnished with sliding panel



# SLIDING BOARD SYSTEMS Horizontal and Vertical



Claridge custom sliding units are ideal for tight spaces where more writable wall space is needed for brainstorming, idea sharing, quick meetings, or training sessions.

- Sliding panels are top-suspended and glide easily over aluminum track on molded nylon roller
- Fixed back panels with 2,3, or 4 sliding panels on 2, 3, or 4 tracks
- Sliding panels and back panels available in a variety of materials
- LCS<sup>3</sup> Porcelain<sup>®</sup> doubles as a magnetic surface with metal backing




# TRACK SYSTEM WITH DOUBLE-SIDED PANELS




## TRAK-IT SLIDING SYSTEM

Flexible communication tools for training rooms, meeting rooms and collaborative spaces

- Double-sided panels multiply communication space
- Panels, available in sizes up to 3' x 4', hang landscape or portrait
- Boards can be positioned anywhere along track
- Easy to rearrange – swing out, lift up
- Available in whiteboard or tackboard surface
- Magnetic marker tray optional



Panels and rail sold separately




# XCHANGE & ENVISION GRAPHIC BOARDS

## XCHANGE GRAPHIC BOARDS


Glass whiteboard features an interchangeable graphic insert that slides easily behind clear, low-iron tempered glass writing surface.

- Exchange scene, season or message by sliding custom graphic in place
- Low profile aluminum trim top and bottom
- Built-in marker rail at top
- Standard black or white Powder Coat finish
- Available in three sizes – 18 x 24", 24" x 36" and 36" x 48"




## ENVISION GRAPHIC BOARDS


- Dry-erase whiteboard surface with digitally printed graphics – photo quality images, logos, etc.
- Envision it: Patient room boards, calendars, planners, performance tracking
- Turn any graphic into a dry erase surface



# TACK WALLS



- Edge-wrapped tackable panels can be custom-made to fit any space
- Cover an entire wall, floor to ceiling
- Ideal for offices, board rooms, conference rooms, etc.
- Choose from Guilford, Carnegie and Maharam fabrics; custom colors or COM fabrics




# GLASS MARKER WALLS



Exceptionally durable, virtually maintenance free, Glass Marker Walls are the hottest thing to hit the office, boardroom or classroom.

- Low-iron tempered glass for exceptional clarity
- 10 standard colors; 180 optional colors
- Available in heights up to 8'
- Narrow face aluminum trim top and bottom

Narrow face  
aluminum trim  
for mounting



*Magnetic accessories on page 26; Standard color options on page 27*



# MARKER WALLS



Ultra-smooth LCS<sup>3</sup> Porcelain® surface supports easy writing and erasing – over and over again. Porcelain surface will not tear like vinyl wallcoverings used for dry-erase and is much more difficult to scratch than painted-on dry-erase surfaces.

- A magnetic writing wall ideal for non-stop brainstorming and client presentations
- Large-scale documents stay in place with standard magnets
- Low gloss surface ideal for use with numerous interactive devices as well as Ultra-short throw projectors
- Butt together for continuous writing surface – cover an entire wall, floor-to-ceiling



# SLIDING GLASS WALL SYSTEMS



- Sliding panels are top-suspended and glide easily over aluminum track on molded nylon roller
- Claridge Glass doubles as a magnetic surface with metal backing
- Claridge Glass is an ultra clear writing surface that won't ghost or stain
- Covers an entire wall, floor-to-ceiling, up to 8' high
- Resists humidity and fading




# SLIDING PORCELAIN WALL SYSTEMS



- Sliding panels are top-suspended and glide easily over aluminum track on molded nylon roller
- LCS<sup>3</sup> Porcelain<sup>®</sup> accepts magnetic accessories
- Covers an entire wall, floor-to-ceiling, up to 8' high
- Resists humidity and fading
- LCS<sup>3</sup> Porcelain<sup>®</sup> surfaces have lifetime warranty



# ACCESSORIES



Dry-erase markers




Microfiber eraser cloth



Whiteboard Cleaner



Partition panel clip



Magnetic aluminum marker tray



Magnetic wood marker tray



Adhesive-backed marker tray

## Magnetic Glass Whiteboard Accessories



Rare earth magnets



Magnetic black felt eraser



Magnetic marker tray



Magnetic marker caddy



Magnetic marker and eraser cloth caddy


# Quality Construction. Expert Craftsmanship.

## Custom Capabilities

- **Aluminum:** Extruded stock and custom anodized shapes and trim
- **Powder Coating:** Two powder coating facilities for standard and custom colors
- **Porcelain Enameling Plant:** State-of-the-art porcelain plant to product the best writing surface on the market today
- **Fabrication:** Assembly, shearing, bending, cutting and sawing raw materials to make stock and custom visual display products
- **Painting and Staining:** In-house painting and wood finishing
- **Graphics:** Full-color, permanently fused graphic capabilities
- **Wood Shop:** Stock and custom shapes made from raw lumber on our own milling equipment
- **Engineering and Design:** Draftsman and engineers available to create custom products to fit any environment
- **Total Fulfillment:** Quality. Service. Innovation. Craftsmanship. Custom and made-to-order products. Fast, reliable shipments.
- **Distribution:** 3 manufacturing plants and 5 distribution centers across the United States



## Standard Magnetic Glass Colors



\* Standard whiteboard color comes in Brilliant White.

Available in 180 optional colors and unlimited custom colors.

## LCS<sup>3</sup> Porcelain® Colors    NP<sup>3</sup> Chalkboard Colors



# MATERIALS, FINISHES & COLORS

## Fabric Options

### Guilford Bailey



Baxter Beige  
GB011



Belmont Silver  
GB010




Khaki  
GB012




Sherman Pewter  
GB024

### Guilford Anchorage




Green Apple  
GA087




Fossil  
GA093

### Guilford Network Patterns




Hickory  
GN011



Putty  
GN031

### Maharam Messenger




Hydrangea  
MM050



Zinc  
MM010




Balsa  
MM001



Ash  
MM077



Cloud  
MM031



Vibrant  
MM070

### Carnegie Nexus



Dune  
CN912



Oatmeal  
CN908



Stone Manor  
CQ99



Windswept  
CQ94

### Carnegie Quarry

*Colors are produced with reasonable accuracy.*

Ask about additional  
Bailey, Anchorage, Network Messenger, Nexus  
and Quarry color options.

## Cork Options



Mushroom  
1108



Buff  
1109




Fawn  
1110



Tan  
1100



Cinnamon  
1104




Oyster  
1103




Smoke  
1111



Steel Gray  
1113



Graphite  
1136



Black  
1132



Salsa  
1117



Tangerine  
1118



Pineapple  
1119




Lettuce  
1120



Blueberry  
1129

### Textured Finishes



Bonded Silver  
Vein PEBS98802




Antique Copper  
Vein PPLS98550

# MATERIALS, FINISHES & COLORS

## MIX Options

### MIX Contemporary Base, Accent Strip & Shelf



Signal White  
RAL9003




Slate Grey  
RAL7015



Matte Black  
302P

### MIX Industrial Base & Shelf



Matte Clear

### MIX Industrial Accent Strip




Matte Black  
302P


### MIX Wood Finish Options




Clear



Vellum



Driftwood



Rustic

## Wood Finish Options



Maple



Mahogany



Cherry



Walnut



Espresso



Ebony

Custom wood finishes optional

## Aluminum Trim Colors



Oyster White  
RAL1013



Signal Yellow  
RAL1003



Traffic Orange  
RAL2009



Red Lilac  
RAL4001



Signal Blue  
RAL5005



Moss Green  
RAL6005



Chocolate Brown  
RAL8017



Silver Grey  
RAL7001



Light Ivory  
RAL1015



Zinc Yellow  
RAL1018



Ruby Red  
RAL3003



Claret Violet  
RAL4004



Cobalt Blue  
RAL5013



Traffic Green  
RAL6024



Pale Brown  
RAL8025



Steel Grey  
RAL7015



Traffic Red  
RAL3020



Strawberry Red  
RAL3018



Ultramarine Blue  
RAL5002




Violet Vluce  
RAL5000



Sky Blue  
RAL5015



Leaf Green  
RAL6002



Signal White  
RAL9003



Jet Black  
RAL9005

Select from 24 Standard Powder Coat Colors and over 180 optional colors



Talk to a Claridge writing surface expert today to learn how we turn workspaces into idea places.